

Data Path : Z:\pestpcbsrv\HPCHEM1\ECD_P\Data\PP092722\
 Data File : PP051684.D
 Signal(s) : Signal #1: ECD1A.ch Signal #2: ECD2B.ch
 Acq On : 27 Sep 2022 11:49
 Operator : YP\AJ
 Sample : N4790-01
 Misc :
 ALS Vial : 11 Sample Multiplier: 1

Instrument :
 ECD_P
 ClientSampleId :
 250FERRYBLVD-SOIL-1

Integration File signal 1: autoint1.e
 Integration File signal 2: autoint2.e
 Quant Time: Sep 27 13:16:27 2022
 Quant Method : Z:\pestpcbsrv\HPCHEM1\ECD_P\methods\PP091922.M
 Quant Title : GC EXTRACTABLES
 QLast Update : Tue Sep 20 14:37:22 2022
 Response via : Initial Calibration
 Integrator: ChemStation

Volume Inj. : 2 µl
 Signal #1 Phase : ZB-MR1 Signal #2 Phase: ZB-MR2
 Signal #1 Info : 30Mx0.32mmx 0.50µ Signal #2 Info : 30M x 0.32mm x 0.25µm

Compound	RT#1	RT#2	Resp#1	Resp#2	ng/ml	ng/ml

System Monitoring Compounds						
1) SA Tetrachlo...	4.429	3.680	30535005	22167776	17.183	14.675
2) SA Decachlor...	10.253	8.780	382.0E6	325.3E6	247.155	271.482
Target Compounds						
41) L9 AR-1268-1	8.704	7.644	5673.8E6	4250.5E6	28167.390	22548.528
42) L9 AR-1268-2	8.799	7.710	6619.9E6	5352.0E6	36080.763	31954.685
43) L9 AR-1268-3	9.034	7.919	1204.5E6	1020.2E6	7464.626	7122.325
44) L9 AR-1268-4	9.473	8.210	3959.9E6	3052.8E6	56463.361	53874.895
45) L9 AR-1268-5	9.901	8.513	5468.1E6	4473.4E6	11101.201	10460.465

(f)=RT Delta > 1/2 Window (#)=Amounts differ by > 25% (m)=manual int.

Data Path : Z:\pestpcbsrv\HPCHEM1\ECD_P\Data\PP092722\
Data File : PP051684.D
Signal(s) : Signal #1: ECD1A.ch Signal #2: ECD2B.ch
Acq On : 27 Sep 2022 11:49
Operator : YP\AJ
Sample : N4790-01
Misc :
ALS Vial : 11 Sample Multiplier: 1

Instrument :
ECD_P
ClientSampleId :
250FERRYBLVD-SOIL-1

Integration File signal 1: autoint1.e
Integration File signal 2: autoint2.e
Quant Time: Sep 27 13:16:27 2022
Quant Method : Z:\pestpcbsrv\HPCHEM1\ECD_P\methods\PP091922.M
Quant Title : GC EXTRACTABLES
QLast Update : Tue Sep 20 14:37:22 2022
Response via : Initial Calibration
Integrator: ChemStation

Volume Inj. : 2 µl
Signal #1 Phase : ZB-MR1 Signal #2 Phase: ZB-MR2
Signal #1 Info : 30Mx0.32mmx 0.50µm Signal #2 Info : 30M x 0.32mm x 0.25µm

