

Data Path : Z:\pestpcbsrv\HPCHEM1\ECD_P\Data\PP060822\
 Data File : PP048516.D
 Signal(s) : Signal #1: ECD1A.ch Signal #2: ECD2B.ch
 Acq On : 07 Jun 2022 16:47
 Operator : YP\AJ
 Sample : N3183-17
 Misc :
 ALS Vial : 28 Sample Multiplier: 1

Instrument :
 ECD_P
 ClientSampleId :
 ESB004N12W2(0-0.5)

Integration File signal 1: autoint1.e
 Integration File signal 2: autoint2.e
 Quant Time: Jun 08 03:06:50 2022
 Quant Method : Z:\pestpcbsrv\HPCHEM1\ECD_P\methods\PP060722.M
 Quant Title : GC EXTRACTABLES
 QLast Update : Tue Jun 07 11:09:40 2022
 Response via : Initial Calibration
 Integrator: ChemStation

Volume Inj. : 2 µl
 Signal #1 Phase : ZB-MR1 Signal #2 Phase: ZB-MR2
 Signal #1 Info : 30Mx0.32mmx 0.50µ Signal #2 Info : 30M x 0.32mm x 0.25µm

Compound	RT#1	RT#2	Resp#1	Resp#2	ng/ml	ng/ml

System Monitoring Compounds						
1) SA Tetrachlo...	4.035	3.204	38056090	31824032	15.882	16.720
2) SA Decachlor...	10.385	8.623	39959748	25774165	20.965	21.048
Target Compounds						
31) L7 AR-1260-1	7.095	5.963	7136.1E6	5094.4E6	68487.529	60373.479
32) L7 AR-1260-2	7.382	6.170	8595.6E6	6150.2E6	70590.569	60043.364
33) L7 AR-1260-3	7.779	6.335	6474.6E6	6133.7E6	76477.846	63291.245
34) L7 AR-1260-4	8.032	6.851	8774.7E6	5044.3E6	84810.958	71269.261
35) L7 AR-1260-5	8.394	7.116	14101.8E6	9846.3E6	72037.049	61312.328

(f)=RT Delta > 1/2 Window (#)=Amounts differ by > 25% (m)=manual int.

Data Path : Z:\pestpcbsrv\HPCHEM1\ECD_P\Data\PP060822\
Data File : PP048516.D
Signal(s) : Signal #1: ECD1A.ch Signal #2: ECD2B.ch
Acq On : 07 Jun 2022 16:47
Operator : YP\AJ
Sample : N3183-17
Misc :
ALS Vial : 28 Sample Multiplier: 1

Instrument :
ECD_P
ClientSampleId :
ESB004N12W2(0-0.5)

Integration File signal 1: autoint1.e
Integration File signal 2: autoint2.e
Quant Time: Jun 08 03:06:50 2022
Quant Method : Z:\pestpcbsrv\HPCHEM1\ECD_P\methods\PP060722.M
Quant Title : GC EXTRACTABLES
QLast Update : Tue Jun 07 11:09:40 2022
Response via : Initial Calibration
Integrator: ChemStation

Volume Inj. : 2 µl
Signal #1 Phase : ZB-MR1 Signal #2 Phase: ZB-MR2
Signal #1 Info : 30Mx0.32mmx 0.50µ Signal #2 Info : 30M x 0.32mm x 0.25µm

