



PERCENT SOLID

Supervisor: apatel  
Analyst: JIGNESH  
Date: 4/30/2021

OVENTEMP IN Celsius(°C): 107  
Time IN: 16:30  
In Date: 04/28/2021  
Weight Check 1.0g: 1.00  
Weight Check 10g: 10.00  
OvenID: M OVEN-1

OVENTEMP OUT Celsius(°C): 103  
Time OUT: 08:22  
Out Date: 04/29/2021  
Weight Check 1.0g: 1.00  
Weight Check 10g: 10.00  
BalanceID: M SC-4  
Thermometer ID: %SOLIDS-OVEN

QC:LB114188

| Lab ID   | Client SampleID       | Dish # | Dish Wt (g) (A) | Dish + Sample Wt (g) (B) | Dish+Dry Sample Wt (g) (C) | % Solid | Comments      |
|----------|-----------------------|--------|-----------------|--------------------------|----------------------------|---------|---------------|
| M2185-01 | N096290-07            | 1      | 1.14            | 9.95                     | 1.54                       | 4.5     | SLUDGE SAMPLE |
| M2185-02 | N096290-08            | 2      | 1.19            | 9.92                     | 1.44                       | 2.9     | SLUDGE SAMPLE |
| M2185-03 | N096290-01            | 3      | 1.16            | 9.98                     | 1.3                        | 1.6     | SLUDGE SAMPLE |
| M2185-04 | N096290-02            | 4      | 1.16            | 9.96                     | 1.43                       | 3.1     | SLUDGE SAMPLE |
| M2185-05 | N096290-06            | 5      | 1.18            | 9.97                     | 1.47                       | 3.3     | SLUDGE SAMPLE |
| M2202-01 | 290                   | 31     | 1.16            | 9.98                     | 4.3                        | 35.6    | SLUDGE SAMPLE |
| M2203-01 | 309                   | 32     | 1.00            | 2.00                     | 2.00                       | 100.0   | PLASTIC       |
| M2204-01 | OILY-DEBRIS-1907-1910 | 57     | 1.16            | 9.86                     | 5.99                       | 55.5    |               |
| M2204-03 | DIESEL-1900           | 58     | 1.00            | 2.00                     | 2.00                       | 100.0   | DIESEL        |
| M2205-01 | KQA103H-END-4-1       | 37     | 1.00            | 2.00                     | 2.00                       | 100.0   | PILC REEL     |
| M2205-02 | KQA103H-END-4-2       | 38     | 1.00            | 2.00                     | 2.00                       | 100.0   | PILC REEL     |
| M2205-03 | KQA103H-END-4-3       | 39     | 1.00            | 2.00                     | 2.00                       | 100.0   | PILC REEL     |
| M2205-04 | KQA103H-END-5-1       | 40     | 1.00            | 2.00                     | 2.00                       | 100.0   | PILC REEL     |
| M2205-05 | KQA103H-END-5-2       | 41     | 1.00            | 2.00                     | 2.00                       | 100.0   | PILC REEL     |
| M2205-06 | KQA103H-END-5-3       | 42     | 1.00            | 2.00                     | 2.00                       | 100.0   | PILC REEL     |
| M2205-08 | MH-306-END-1          | 43     | 1.00            | 2.00                     | 2.00                       | 100.0   | PILC REEL     |
| M2205-09 | MH-306-END-2          | 44     | 1.00            | 2.00                     | 2.00                       | 100.0   | PILC REEL     |
| M2205-10 | KQA103H-END-1-1       | 45     | 1.00            | 2.00                     | 2.00                       | 100.0   | PILC REEL     |
| M2205-11 | KQA103H-END-1-2       | 46     | 1.00            | 2.00                     | 2.00                       | 100.0   | PILC REEL     |
| M2205-12 | KQA103H-END-2-1       | 47     | 1.00            | 2.00                     | 2.00                       | 100.0   | PILC REEL     |
| M2205-13 | KQA103H-END-2-2       | 48     | 1.00            | 2.00                     | 2.00                       | 100.0   | PILC REEL     |
| M2205-14 | KQA103H-END-2-3       | 49     | 1.00            | 2.00                     | 2.00                       | 100.0   | PILC REEL     |
| M2205-15 | KQA103H-END-3-1       | 50     | 1.00            | 2.00                     | 2.00                       | 100.0   | PILC REEL     |
| M2205-16 | KQA103H-END-3-2       | 51     | 1.00            | 2.00                     | 2.00                       | 100.0   | PILC REEL     |
| M2205-17 | KQA103H-END-3-3       | 52     | 1.00            | 2.00                     | 2.00                       | 100.0   | PILC REEL     |
| M2207-01 | TP-6A-5-COMP          | 33     | 1.18            | 9.76                     | 8.32                       | 83.2    |               |
| M2207-02 | TP-6A-EPH-2           | 34     | 1.15            | 9.96                     | 8.6                        | 84.6    |               |
| M2207-03 | TP-4A-3-COMP          | 35     | 1.18            | 9.71                     | 8.64                       | 87.5    |               |



PERCENT SOLID

Supervisor: apatel  
Analyst: JIGNESH  
Date: 4/30/2021

OVENTEMP IN Celsius(°C): 107  
Time IN: 16:30  
In Date: 04/28/2021  
Weight Check 1.0g: 1.00  
Weight Check 10g: 10.00  
OvenID: M OVEN-1

OVENTEMP OUT Celsius(°C): 103  
Time OUT: 08:22  
Out Date: 04/29/2021  
Weight Check 1.0g: 1.00  
Weight Check 10g: 10.00  
BalanceID: M SC-4  
Thermometer ID: %SOLIDS-OVEN

QC:LB114188

| Lab ID   | Client SampleID | Dish # | Dish Wt (g) (A) | Dish + Sample Wt (g) (B) | Dish+Dry Sample Wt (g) (C) | % Solid | Comments                |
|----------|-----------------|--------|-----------------|--------------------------|----------------------------|---------|-------------------------|
| M2207-04 | TP-4A-3-EPH-2   | 36     | 1.16            | 9.98                     | 8.97                       | 88.5    |                         |
| M2211-01 | HA-51           | 6      | 1.00            | 2.00                     | 2.00                       | 100.0   | CAULKING                |
| M2214-01 | PT-AN-SOIL      | 7      | 1.00            | 2.00                     | 2.00                       | 100.0   | p.e.sample              |
| M2214-02 | PT-CORR-SOIL    | 8      | 1.00            | 2.00                     | 2.00                       | 100.0   | p.e.sample              |
| M2214-03 | PT-CORR-SOIL    | 9      | 1.00            | 2.00                     | 2.00                       | 100.0   | p.e.sample              |
| M2214-04 | PT-CN-SOIL      | 10     | 1.00            | 2.00                     | 2.00                       | 100.0   | p.e.sample              |
| M2214-05 | PT-CN-SOIL      | 11     | 1.00            | 2.00                     | 2.00                       | 100.0   | p.e.sample              |
| M2214-06 | PT-FP-SOIL      | 12     | 1.00            | 2.00                     | 2.00                       | 100.0   | p.e.sample              |
| M2214-07 | PT-CR6-SOIL     | 13     | 1.00            | 2.00                     | 2.00                       | 100.0   | p.e.sample              |
| M2214-08 | PT-NUT-SOIL     | 14     | 1.00            | 2.00                     | 2.00                       | 100.0   | p.e.sample              |
| M2214-09 | PT-NUT-SOIL     | 15     | 1.00            | 2.00                     | 2.00                       | 100.0   | p.e.sample              |
| M2214-10 | PT-OGR-SOIL     | 16     | 1.00            | 2.00                     | 2.00                       | 100.0   | p.e.sample              |
| M2214-11 | PT-MET-SOIL     | 17     | 1.00            | 2.00                     | 2.00                       | 100.0   | p.e.sample              |
| M2214-12 | PT-BNA-SOIL     | 18     | 1.00            | 2.00                     | 2.00                       | 100.0   | p.e.sample              |
| M2214-13 | PT-PAH-SOIL     | 19     | 1.00            | 2.00                     | 2.00                       | 100.0   | p.e.sample              |
| M2214-14 | PT-DIES-SOIL    | 20     | 1.00            | 2.00                     | 2.00                       | 100.0   | p.e.sample              |
| M2214-15 | PT-GAS-SOIL     | 21     | 1.00            | 2.00                     | 2.00                       | 100.0   | p.e.sample              |
| M2214-16 | PT-NJEPH-SOIL   | 22     | 1.00            | 2.00                     | 2.00                       | 100.0   | p.e.sample              |
| M2214-17 | PT-HERB-SOIL    | 23     | 1.00            | 2.00                     | 2.00                       | 100.0   | p.e.sample              |
| M2214-18 | PT-PCB-SOIL     | 24     | 1.00            | 2.00                     | 2.00                       | 100.0   | p.e.sample              |
| M2214-19 | PT-PEST-SOIL    | 25     | 1.00            | 2.00                     | 2.00                       | 100.0   | p.e.sample              |
| M2214-20 | PT-CHLR-SOIL    | 26     | 1.00            | 2.00                     | 2.00                       | 100.0   | p.e.sample              |
| M2214-21 | PT-TXP-SOIL     | 27     | 1.00            | 2.00                     | 2.00                       | 100.0   | p.e.sample              |
| M2214-22 | PT-VOA-SOIL     | 28     | 1.00            | 2.00                     | 2.00                       | 100.0   | p.e.sample              |
| M2214-23 | PT-SOL-SOIL     | 29     | 1.16            | 8.93                     | 7.28                       | 78.8    |                         |
| M2214-24 | PT-PCBO-SOIL    | 30     | 1.00            | 2.00                     | 2.00                       | 100.0   | OIL SAMPLE, p.e. sample |
| M2216-01 | KZH01ZP-END-1-1 | 53     | 1.00            | 2.00                     | 2.00                       | 100.0   | PILC REEL               |
| M2216-02 | KZH01ZP-END-1-2 | 54     | 1.00            | 2.00                     | 2.00                       | 100.0   | PILC REEL               |



PERCENT SOLID

Supervisor: apatel  
Analyst: JIGNESH  
Date: 4/30/2021

OVENTEMP IN Celsius(°C): 107  
Time IN: 16:30  
In Date: 04/28/2021  
Weight Check 1.0g: 1.00  
Weight Check 10g: 10.00  
OvenID: M OVEN-1

OVENTEMP OUT Celsius(°C): 103  
Time OUT: 08:22  
Out Date: 04/29/2021  
Weight Check 1.0g: 1.00  
Weight Check 10g: 10.00  
BalanceID: M SC-4  
Thermometer ID: %SOLIDS-OVEN

QC:LB114188

| Lab ID    | Client SampleID         | Dish # | Dish Wt(g) (A) | Dish + Sample Wt(g) (B) | Dish+Dry Sample Wt(g) (C) | % Solid | Comments  |
|-----------|-------------------------|--------|----------------|-------------------------|---------------------------|---------|-----------|
| M2216-03  | KZH01ZP-END-2-1         | 55     | 1.00           | 2.00                    | 2.00                      | 100.0   | PILC REEL |
| M2216-04  | KZH01ZP-END-2-2         | 56     | 1.00           | 2.00                    | 2.00                      | 100.0   | PILC REEL |
| M2218-01  | FK-BPM-01-C6-D6-C6A-D6A | 59     | 1.15           | 9.95                    | 9.00                      | 89.2    |           |
| M2218-02  | FK-BPM-01-C6-D6-C6A-D6A | 60     | 1.19           | 9.96                    | 9.07                      | 89.9    |           |
| M2219-01  | FK-PS-01-071            | 61     | 1.14           | 9.94                    | 8.47                      | 83.3    |           |
| M2219-01D | FK-PS-01-071DUP         | 62     | 1.16           | 9.96                    | 8.49                      | 83.3    |           |
| M2219-02  | FK-PS-01-071            | 63     | 1.14           | 9.98                    | 8.69                      | 85.4    |           |
| M2222-01  | TP-5-COMP               | 67     | 1.18           | 9.53                    | 8.2                       | 84.1    |           |
| M2222-04  | TP-5-EPH-2              | 68     | 1.15           | 9.97                    | 8.75                      | 86.2    |           |
| M2222-05  | TP-5-VOC-TCL            | 69     | 1.17           | 9.97                    | 8.17                      | 79.5    |           |
| M2222-06  | TP-5A-COMP              | 70     | 1.12           | 9.93                    | 8.81                      | 87.3    |           |
| M2222-09  | TP-5A-EPH-2             | 71     | 1.17           | 9.62                    | 8.78                      | 90.1    |           |
| M2222-10  | TP-5A-VOC-TCL           | 72     | 1.18           | 9.98                    | 8.97                      | 88.5    |           |
| M2223-01  | LOADING-AREA-MUD        | 64     | 1.15           | 9.95                    | 8.16                      | 79.7    |           |
| M2223-02  | SIDE-OF-TENT            | 65     | 1.18           | 9.92                    | 6.96                      | 66.1    |           |
| M2223-03  | LOADING-AREA-PAD        | 66     | 1.00           | 2.00                    | 2.00                      | 100.0   | PADS      |

$$\% \text{ Solid} = \frac{(C-A) * 100}{(B-A)}$$