



PERCENT SOLID

Supervisor: mohammad

Analyst: jignesh

Date: 5/9/2022

OVENTEMP IN Celsius(°C): 107

Time IN: 17:15

In Date: 05/06/2022

Weight Check 1.0g: 1.00

Weight Check 10g: 10.00

OvenID: M OVEN-1

OVENTEMP OUT Celsius(°C): 103

Time OUT: 08:25

Out Date: 05/07/2022

Weight Check 1.0g: 1.00

Weight Check 10g: 10.00

BalanceID: M SC-4

Thermometer ID: %SOLIDS-OVEN

QC:LB120023

| Lab ID   | Client SampleID      | Dish # | Dish Wt (g) (A) | Sample Wt (g) | Dish + Sample Wt (g) (B) | Dish+Dry Sample Wt (g) (C) | % Solid | Comments                 |
|----------|----------------------|--------|-----------------|---------------|--------------------------|----------------------------|---------|--------------------------|
| N2712-01 | SP-1                 | 1      | 0.91            | 8.99          | 9.9                      | 9.55                       | 96.1    |                          |
| N2712-02 | SP-1-EPH-2           | 2      | 0.91            | 8.99          | 9.9                      | 9.55                       | 96.1    |                          |
| N2712-03 | SP-2                 | 3      | 0.91            | 8.95          | 9.86                     | 9.51                       | 96.1    |                          |
| N2712-04 | SP-2-EPH-2           | 4      | 0.91            | 8.95          | 9.86                     | 9.51                       | 96.1    |                          |
| N2712-05 | SP-3                 | 5      | 0.91            | 8.94          | 9.85                     | 9.43                       | 95.3    |                          |
| N2712-06 | SP-3-EPH-2           | 6      | 0.93            | 8.71          | 9.64                     | 9.43                       | 97.6    |                          |
| N2712-07 | TP-1                 | 7      | 0.92            | 8.78          | 9.7                      | 8.7                        | 88.6    |                          |
| N2712-08 | TP-1-EPH-2           | 8      | 0.92            | 8.78          | 9.7                      | 8.7                        | 88.6    |                          |
| N2712-09 | TP-2                 | 9      | 0.92            | 8.72          | 9.64                     | 8.65                       | 88.6    |                          |
| N2712-10 | TP-2-EPH-2           | 10     | 0.92            | 8.72          | 9.64                     | 8.65                       | 88.6    |                          |
| N2712-11 | TP-3                 | 11     | 0.92            | 8.98          | 9.9                      | 8.97                       | 89.6    |                          |
| N2712-12 | TP-3-EPH-2           | 12     | 0.92            | 8.98          | 9.9                      | 8.97                       | 89.6    |                          |
| N2725-01 | TRE-1254             | 51     | 0.93            | 9.01          | 9.94                     | 8.45                       | 83.5    |                          |
| N2725-02 | TRE-1284             | 13     | 0.91            | 9.03          | 9.94                     | 9.66                       | 96.9    |                          |
| N2732-01 | 050522AP01-PCB       | 14     | 1.00            | 1.00          | 2.00                     | 2.00                       | 100.0   | bulk paint               |
| N2737-01 | PE-A1                | 25     | 0.92            | 9.01          | 9.93                     | 9.14                       | 91.2    |                          |
| N2737-02 | SW-N-A1              | 26     | 0.91            | 9.05          | 9.96                     | 8.13                       | 79.8    |                          |
| N2738-01 | 2463                 | 43     | 1.00            | 1.00          | 2.00                     | 2.00                       | 100.0   | debris                   |
| N2738-02 | 2468                 | 44     | 1.00            | 1.00          | 2.00                     | 2.00                       | 100.0   | DESSICANT                |
| N2738-03 | 2474                 | 45     | 1.00            | 1.00          | 2.00                     | 2.00                       | 100.0   | STONE SAMPLE,100% SOLIDS |
| N2738-04 | 2474-EPH-2           | 46     | 1.00            | 1.00          | 2.00                     | 2.00                       | 100.0   | STONE SAMPLE,100% SOLIDS |
| N2739-01 | 124030               | 27     | 0.9             | 8.74          | 9.64                     | 7.43                       | 74.7    |                          |
| N2739-03 | 124055               | 28     | 0.91            | 8.79          | 9.7                      | 7.25                       | 72.1    | GEL MATRIX               |
| N2739-05 | 124035               | 29     | 0.95            | 8.83          | 9.78                     | 8.57                       | 86.3    |                          |
| N2739-07 | 124042               | 30     | 0.94            | 9.04          | 9.98                     | 7.9                        | 77.0    |                          |
| N2740-05 | SVOC-GPC-BLANK       | 15     | 1.00            | 1.00          | 2.00                     | 2.00                       | 100.0   |                          |
| N2740-06 | PEST-GPC-BLANK       | 16     | 1.00            | 1.00          | 2.00                     | 2.00                       | 100.0   |                          |
| N2740-07 | PEST-GPC-BLANK-SPIKE | 17     | 1.00            | 1.00          | 2.00                     | 2.00                       | 100.0   |                          |



# PERCENT SOLID

Supervisor: mohammad

Analyst: jignesh

Date: 5/9/2022

OVENTEMP IN Celsius(°C): 107

Time IN: 17:15

In Date: 05/06/2022

Weight Check 1.0g: 1.00

Weight Check 10g: 10.00

OvenID: M OVEN-1

OVENTEMP OUT Celsius(°C): 103

Time OUT: 08:25

Out Date: 05/07/2022

Weight Check 1.0g: 1.00

Weight Check 10g: 10.00

BalanceID: M SC-4

Thermometer ID: %SOLIDS-OVEN

QC:LB120023

| Lab ID   | Client SampleID       | Dish # | Dish Wt (g) (A) | Sample Wt (g) | Dish + Sample Wt (g) (B) | Dish+Dry Sample Wt (g) (C) | % Solid | Comments               |
|----------|-----------------------|--------|-----------------|---------------|--------------------------|----------------------------|---------|------------------------|
| N2740-08 | PCB-GPC-BLANK         | 18     | 1.00            | 1.00          | 2.00                     | 2.00                       | 100.0   |                        |
| N2740-09 | PCB-GPC-BLANK-SPIKE   | 19     | 1.00            | 1.00          | 2.00                     | 2.00                       | 100.0   |                        |
| N2740-10 | SVOC-GPC2-BLANK       | 20     | 1.00            | 1.00          | 2.00                     | 2.00                       | 100.0   |                        |
| N2740-11 | PEST-GPC2-BLANK       | 21     | 1.00            | 1.00          | 2.00                     | 2.00                       | 100.0   |                        |
| N2740-12 | PEST-GPC2-BLANK-SPIKE | 22     | 1.00            | 1.00          | 2.00                     | 2.00                       | 100.0   |                        |
| N2740-13 | PCB-GCP2-BLANK        | 23     | 1.00            | 1.00          | 2.00                     | 2.00                       | 100.0   |                        |
| N2740-14 | PCB-GCP2-BLANK-SPIKE  | 24     | 1.00            | 1.00          | 2.00                     | 2.00                       | 100.0   |                        |
| N2742-01 | COMP-1                | 31     | 1.00            | 1.00          | 2.00                     | 2.00                       | 100.0   | debris                 |
| N2742-02 | COMP-2                | 32     | 1.00            | 1.00          | 2.00                     | 2.00                       | 100.0   | PLASTIC- debris sample |
| N2743-01 | SOM-2022-27A          | 33     | 1.00            | 1.00          | 2.00                     | 2.00                       | 100.0   | PILC REEL              |
| N2743-02 | SOM-2022-28A          | 34     | 1.00            | 1.00          | 2.00                     | 2.00                       | 100.0   | PILC REEL              |
| N2743-03 | SOM-2022-28B          | 35     | 1.00            | 1.00          | 2.00                     | 2.00                       | 100.0   | PILC REEL              |
| N2743-04 | SOM-2022-29A          | 36     | 1.00            | 1.00          | 2.00                     | 2.00                       | 100.0   | PILC REEL              |
| N2743-05 | SOM-2022-29B          | 37     | 1.00            | 1.00          | 2.00                     | 2.00                       | 100.0   | PILC REEL              |
| N2743-06 | SOM-2022-30A          | 38     | 1.00            | 1.00          | 2.00                     | 2.00                       | 100.0   | PILC REEL              |
| N2743-07 | SOM-2022-31A          | 39     | 1.00            | 1.00          | 2.00                     | 2.00                       | 100.0   | PILC REEL              |
| N2743-08 | SOM-2022-31B          | 40     | 1.00            | 1.00          | 2.00                     | 2.00                       | 100.0   | PILC REEL              |
| N2743-09 | SOM-2022-32A          | 41     | 1.00            | 1.00          | 2.00                     | 2.00                       | 100.0   | PILC REEL              |
| N2743-10 | SOM-2022-32B          | 42     | 1.00            | 1.00          | 2.00                     | 2.00                       | 100.0   | PILC REEL              |
| N2745-01 | MH-31S                | 47     | 0.93            | 8.78          | 9.71                     | 8.7                        | 88.5    |                        |
| N2745-03 | MH-31S-EPH            | 48     | 0.94            | 8.91          | 9.85                     | 8.74                       | 87.5    |                        |
| N2745-04 | MH-31D                | 49     | 0.93            | 9.04          | 9.97                     | 8.77                       | 86.7    |                        |
| N2745-06 | MH-31D-EPH            | 50     | 0.92            | 9.04          | 9.96                     | 8.93                       | 88.6    |                        |

$$\% \text{ Solid} = \frac{(C-A) * 100}{(B-A)}$$