



PERCENT SOLID

Supervisor: mohammad

Analyst: JIGNESH

Date: 7/14/2022

OVENTEMP IN Celsius(°C): 107

Time IN: 17:10

In Date: 07/13/2022

Weight Check 1.0g: 1.00

Weight Check 10g: 10.00

OvenID: M OVEN-1

OVENTEMP OUT Celsius(°C): 104

Time OUT: 08:22

Out Date: 07/14/2022

Weight Check 1.0g: 1.00

Weight Check 10g: 10.00

BalanceID: M SC-4

Thermometer ID: %SOLIDS-OVEN

QC:LB121037

| Lab ID   | Client SampleID | Dish # | Dish Wt(g) (A) | Sample Wt(g) | Dish + Sample Wt(g) (B) | Dish+Dry Sample Wt(g) (C) | % Solid | Comments  |
|----------|-----------------|--------|----------------|--------------|-------------------------|---------------------------|---------|-----------|
| N3674-01 | CLI-2022-62A    | 1      | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | PILC REEL |
| N3674-02 | CLI-2022-62B    | 2      | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | PILC REEL |
| N3677-01 | 122A            | 3      | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | PILC REEL |
| N3677-02 | 122B            | 4      | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | PILC REEL |
| N3677-03 | 123A            | 5      | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | PILC REEL |
| N3677-04 | 123B            | 6      | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | PILC REEL |
| N3677-05 | 119A            | 7      | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | PILC REEL |
| N3677-06 | 119B            | 8      | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | PILC REEL |
| N3677-07 | 120             | 9      | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | PILC REEL |
| N3677-08 | 121             | 10     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | PILC REEL |
| N3680-01 | X127-B6         | 36     | 0.9            | 9.04         | 9.94                    | 8.72                      | 86.5    |           |
| N3680-02 | X127-S6         | 37     | 0.93           | 8.69         | 9.62                    | 8.46                      | 86.7    |           |
| N3680-03 | X127-B5         | 38     | 0.91           | 9.06         | 9.97                    | 7.91                      | 77.3    |           |
| N3680-04 | X127-S5         | 39     | 0.91           | 9.03         | 9.94                    | 9.28                      | 92.7    |           |
| N3680-05 | X127-B4         | 40     | 0.91           | 8.64         | 9.55                    | 7.94                      | 81.4    |           |
| N3680-06 | X127-S4         | 41     | 0.93           | 8.73         | 9.66                    | 9.24                      | 95.2    |           |
| N3680-07 | X127-B3         | 42     | 0.84           | 8.93         | 9.77                    | 9.25                      | 94.2    |           |
| N3680-08 | X127-S3         | 43     | 0.93           | 8.97         | 9.9                     | 8.88                      | 88.6    |           |
| N3680-09 | X127-DUP-2      | 44     | 0.93           | 9.05         | 9.98                    | 8.6                       | 84.8    |           |
| N3684-01 | JEC5015-1-1     | 11     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | PILC REEL |
| N3684-02 | JEC5015-1-2     | 12     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | PILC REEL |
| N3684-03 | BC247799-1-1    | 13     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | PILC REEL |
| N3684-04 | BC247799-1-2    | 14     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | PILC REEL |
| N3684-05 | BC288026-1-1    | 15     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | PILC REEL |
| N3684-06 | BC288026-1-2    | 16     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | PILC REEL |
| N3684-07 | KMA724N-1-1     | 17     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | PILC REEL |
| N3684-08 | KMA724N-1-2     | 18     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | PILC REEL |
| N3684-09 | KMA724N-2-1     | 19     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | PILC REEL |

**PERCENT SOLID****Supervisor:** mohammad**Analyst:** JIGNESH**Date:** 7/14/2022**OVENTEMP IN Celsius(°C):** 107**Time IN:** 17:10**In Date:** 07/13/2022**Weight Check 1.0g:** 1.00**Weight Check 10g:** 10.00**OvenID:** M OVEN-1**OVENTEMP OUT Celsius(°C):** 104**Time OUT:** 08:22**Out Date:** 07/14/2022**Weight Check 1.0g:** 1.00**Weight Check 10g:** 10.00**BalanceID:** M SC-4**Thermometer ID:** %SOLIDS-OVEN**QC:**LB121037

| Lab ID    | Client SampleID | Dish # | Dish Wt(g) (A) | Sample Wt(g) | Dish + Sample Wt(g) (B) | Dish+Dry Sample Wt(g) (C) | % Solid | Comments   |
|-----------|-----------------|--------|----------------|--------------|-------------------------|---------------------------|---------|------------|
| N3684-10  | KMA724N-2-2     | 20     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | PILC REEL  |
| N3686-01  | JEH689V-1-1     | 21     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | PILC REEL  |
| N3686-02  | JEH689V-1-2     | 22     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | PILC REEL  |
| N3686-03  | BC21679-1-1     | 23     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | PILC REEL  |
| N3686-04  | BC21679-1-2     | 24     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | PILC REEL  |
| N3687-01  | ETGI-361        | 25     | 0.91           | 8.84         | 9.75                    | 6.95                      | 68.3    |            |
| N3687-02  | ETGI-361-EPH-2  | 26     | 0.91           | 8.84         | 9.75                    | 6.95                      | 68.3    |            |
| N3687-03  | ETGI-346        | 27     | 0.92           | 9.05         | 9.97                    | 8.56                      | 84.4    |            |
| N3687-04  | ETGI-346-EPH-2  | 28     | 0.92           | 9.05         | 9.97                    | 8.56                      | 84.4    |            |
| N3687-05  | D2584           | 34     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | debris     |
| N3687-06  | D2585           | 35     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | OIL SAMPLE |
| N3688-01  | 72-12016        | 29     | 0.93           | 8.63         | 9.56                    | 9.36                      | 97.7    |            |
| N3688-02  | 72-12016-EPH-2  | 30     | 0.93           | 8.63         | 9.56                    | 9.36                      | 97.7    |            |
| N3688-03  | VNJ-240         | 31     | 0.91           | 9.07         | 9.98                    | 9.19                      | 91.3    |            |
| N3688-04  | VNJ-240-EPH-2   | 32     | 0.91           | 9.07         | 9.98                    | 9.19                      | 91.3    |            |
| N3688-05  | 2359            | 33     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | OIL SAMPLE |
| N3689-01  | S15-01-B        | 46     | 0.92           | 9.00         | 9.92                    | 9.16                      | 91.6    |            |
| N3689-02  | S15-02-B        | 47     | 0.92           | 8.78         | 9.7                     | 8.84                      | 90.2    |            |
| N3689-03  | S15-02-S        | 48     | 0.92           | 8.64         | 9.56                    | 8.94                      | 92.8    |            |
| N3689-04  | DUP-10          | 49     | 0.98           | 8.72         | 9.7                     | 8.89                      | 90.7    |            |
| N3690-01  | S10-01-B        | 50     | 0.92           | 9.05         | 9.97                    | 9.46                      | 94.4    |            |
| N3690-02  | S10-02-B        | 51     | 0.93           | 8.80         | 9.73                    | 7.66                      | 76.5    |            |
| N3690-03  | S10-01-S        | 52     | 0.91           | 9.03         | 9.94                    | 8.78                      | 87.2    |            |
| N3690-04  | DUP-8           | 53     | 0.97           | 8.78         | 9.75                    | 8.52                      | 86.0    |            |
| N3690-05  | S10-02-S        | 54     | 0.93           | 8.73         | 9.66                    | 7.96                      | 80.5    |            |
| N3690-05D | S10-02-SDUP     | 55     | 0.95           | 8.73         | 9.68                    | 7.98                      | 80.5    |            |
| N3693-01  | VNJ-230         | 56     | 0.92           | 9.02         | 9.94                    | 9.55                      | 95.7    |            |
| N3693-02  | VNJ-230         | 57     | 0.9            | 8.82         | 9.72                    | 9.19                      | 94.0    |            |



# PERCENT SOLID

Supervisor: mohammad

Analyst: JIGNESH

Date: 7/14/2022

OVENTEMP IN Celsius(°C): 107

Time IN: 17:10

In Date: 07/13/2022

Weight Check 1.0g: 1.00

Weight Check 10g: 10.00

OvenID: M OVEN-1

OVENTEMP OUT Celsius(°C): 104

Time OUT: 08:22

Out Date: 07/14/2022

Weight Check 1.0g: 1.00

Weight Check 10g: 10.00

BalanceID: M SC-4

Thermometer ID: %SOLIDS-OVEN

QC:LB121037

| Lab ID   | Client SampleID   | Dish # | Dish Wt(g) (A) | Sample Wt(g) | Dish + Sample Wt(g) (B) | Dish+Dry Sample Wt(g) (C) | % Solid | Comments |
|----------|-------------------|--------|----------------|--------------|-------------------------|---------------------------|---------|----------|
| N3694-01 | X127-B1           | 60     | 0.91           | 8.86         | 9.77                    | 7.48                      | 74.2    |          |
| N3694-02 | X127-S1           | 61     | 0.95           | 9.01         | 9.96                    | 7.66                      | 74.5    |          |
| N3694-03 | X127-B2           | 62     | 0.92           | 8.68         | 9.6                     | 8.88                      | 91.7    |          |
| N3694-04 | X127-S2           | 63     | 0.9            | 8.74         | 9.64                    | 9.15                      | 94.4    |          |
| N3694-05 | X127-DUP-1        | 64     | 0.91           | 8.96         | 9.87                    | 8.79                      | 87.9    |          |
| N3695-09 | SPC-01C-84-83     | 45     | 0.91           | 9.06         | 9.97                    | 9.55                      | 95.4    |          |
| N3708-01 | OR-2-071322       | 58     | 0.89           | 9.00         | 9.89                    | 9.18                      | 92.1    |          |
| N3708-02 | OR-2-071322-EPH-2 | 59     | 0.93           | 9.03         | 9.96                    | 9.17                      | 91.3    |          |
| N3712-01 | S16-04-B2         | 65     | 0.92           | 8.96         | 9.88                    | 8.87                      | 88.7    |          |
| N3713-01 | S11-01-B          | 66     | 0.98           | 8.77         | 9.75                    | 7.64                      | 75.9    |          |
| N3713-02 | S11-02-B          | 67     | 0.91           | 8.99         | 9.9                     | 9.11                      | 91.2    |          |
| N3713-03 | S11-03-B          | 68     | 0.93           | 8.70         | 9.63                    | 7.47                      | 75.2    |          |
| N3713-04 | S11-01-S          | 69     | 0.95           | 9.02         | 9.97                    | 8.66                      | 85.5    |          |
| N3713-05 | S11-02-S          | 70     | 0.97           | 8.80         | 9.77                    | 8.55                      | 86.1    |          |
| N3713-06 | S11-03-S          | 71     | 0.91           | 9.03         | 9.94                    | 8.6                       | 85.2    |          |
| N3714-01 | S13-01-B          | 72     | 0.93           | 9.03         | 9.96                    | 9.11                      | 90.6    |          |
| N3714-02 | DUP-9             | 73     | 0.93           | 9.04         | 9.97                    | 8.38                      | 82.4    |          |
| N3714-03 | S13-01-S          | 74     | 0.9            | 9.05         | 9.95                    | 8.1                       | 79.6    |          |
| N3714-04 | S13-02-S          | 75     | 0.89           | 9.05         | 9.94                    | 8.36                      | 82.5    |          |

$$\% \text{ Solid} = \frac{(C-A) * 100}{(B-A)}$$