



PERCENT SOLID

Supervisor: Iwona  
Analyst: jignesh  
Date: 12/14/2022

OVENTEMP IN Celsius(°C): 107  
Time IN: 17:00  
In Date: 12/13/2022  
Weight Check 1.0g: 1.00  
Weight Check 10g: 10.00  
OvenID: M OVEN-1

OVENTEMP OUT Celsius(°C): 103  
Time OUT: 08:33  
Out Date: 12/14/2022  
Weight Check 1.0g: 1.00  
Weight Check 10g: 10.00  
BalanceID: M SC-4  
Thermometer ID: %SOLIDS-OVEN

QC:LB123245

| Lab ID   | Client SampleID  | Dish # | Dish Wt(g) (A) | Sample Wt(g) | Dish + Sample Wt(g) (B) | Dish+Dry Sample Wt(g) (C) | % Solid | Comments    |
|----------|------------------|--------|----------------|--------------|-------------------------|---------------------------|---------|-------------|
| N6026-01 | B-29-SB01        | 1      | 1.14           | 6.69         | 7.83                    | 6.76                      | 84.0    |             |
| N6026-02 | B-29-SB02        | 2      | 1.16           | 4.54         | 5.7                     | 4.56                      | 74.9    |             |
| N6028-01 | PLA-164          | 59     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| N6028-02 | PLA-165          | 60     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| N6028-03 | PLA-166          | 61     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| N6035-01 | BIC-1272         | 3      | 1.12           | 8.49         | 9.61                    | 8.77                      | 90.1    |             |
| N6036-01 | 31916            | 62     | 0.91           | 8.86         | 9.77                    | 6.99                      | 68.6    |             |
| N6036-02 | 1                | 63     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| N6036-03 | 2                | 64     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| N6036-04 | 3                | 65     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| N6036-05 | 4                | 66     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| N6037-01 | RB-16- (2.5-4.5) | 4      | 0.91           | 8.69         | 9.6                     | 8.77                      | 90.4    |             |
| N6037-02 | RB-17- (1-3)     | 5      | 1.16           | 8.75         | 9.91                    | 8.67                      | 85.8    |             |
| N6037-03 | RB-18- (2-4)     | 6      | 1.14           | 8.44         | 9.58                    | 8.79                      | 90.6    |             |
| N6037-04 | RB-19- (2.3-4.3) | 7      | 0.93           | 9.04         | 9.97                    | 8.92                      | 88.4    |             |
| N6037-05 | RB-20- (5-7)     | 8      | 1.16           | 8.69         | 9.85                    | 9.36                      | 94.4    |             |
| N6037-06 | RB-20- (7-9)     | 9      | 0.95           | 9.02         | 9.97                    | 9.41                      | 93.8    |             |
| N6037-07 | RB-21- (6-8)     | 10     | 0.93           | 8.87         | 9.8                     | 8.95                      | 90.4    |             |
| N6037-08 | RB-22- (1-3)     | 11     | 1.11           | 8.73         | 9.84                    | 8.61                      | 85.9    |             |
| N6037-09 | RB-22- (8-10)    | 12     | 1.16           | 8.81         | 9.97                    | 8.75                      | 86.2    |             |
| N6037-10 | N6037-09MS       | 13     | 1.16           | 8.81         | 9.97                    | 8.75                      | 86.2    |             |
| N6037-11 | N6037-09MSD      | 14     | 1.16           | 8.81         | 9.97                    | 8.75                      | 86.2    |             |
| N6037-12 | RB-23- (0.5-2.5) | 15     | 1.15           | 8.67         | 9.82                    | 8.41                      | 83.7    |             |
| N6037-13 | RB-23- (8-10)    | 16     | 1.19           | 8.77         | 9.96                    | 9.7                       | 97.0    |             |
| N6037-14 | RB-24- (1-3)     | 17     | 0.91           | 8.89         | 9.8                     | 9.32                      | 94.6    |             |
| N6037-15 | RB-24- (7-9)     | 18     | 0.91           | 8.95         | 9.86                    | 9.41                      | 95.0    |             |
| N6037-16 | RB-25- (1-3)     | 19     | 0.91           | 8.98         | 9.89                    | 8.37                      | 83.1    |             |
| N6037-17 | RB-25- (7-9)     | 20     | 1.16           | 8.67         | 9.83                    | 8.7                       | 87.0    |             |



PERCENT SOLID

Supervisor: Iwona  
Analyst: jignesh  
Date: 12/14/2022

OVENTEMP IN Celsius(°C): 107  
Time IN: 17:00  
In Date: 12/13/2022  
Weight Check 1.0g: 1.00  
Weight Check 10g: 10.00  
OvenID: M OVEN-1

OVENTEMP OUT Celsius(°C): 103  
Time OUT: 08:33  
Out Date: 12/14/2022  
Weight Check 1.0g: 1.00  
Weight Check 10g: 10.00  
BalanceID: M SC-4  
Thermometer ID: %SOLIDS-OVEN

QC:LB123245

| Lab ID   | Client SampleID | Dish # | Dish Wt(g) (A) | Sample Wt(g) | Dish + Sample Wt(g) (B) | Dish+Dry Sample Wt(g) (C) | % Solid | Comments |
|----------|-----------------|--------|----------------|--------------|-------------------------|---------------------------|---------|----------|
| N6037-18 | N6037-17MS      | 21     | 1.16           | 8.67         | 9.83                    | 8.7                       | 87.0    |          |
| N6037-19 | N6037-17MSD     | 22     | 1.16           | 8.67         | 9.83                    | 8.7                       | 87.0    |          |
| N6037-20 | RB-26-(2-4)     | 23     | 1.14           | 8.47         | 9.61                    | 8.56                      | 87.6    |          |
| N6037-21 | RB-27-(2.5-4.5) | 24     | 0.91           | 9.01         | 9.92                    | 8.68                      | 86.2    |          |
| N6037-22 | RB-27-(5-7)     | 25     | 0.93           | 8.91         | 9.84                    | 8.99                      | 90.5    |          |
| N6037-23 | RB-28-(2.5-4.5) | 26     | 1.12           | 8.81         | 9.93                    | 8.8                       | 87.2    |          |
| N6037-24 | RB-28-(5-7)     | 27     | 1.15           | 8.52         | 9.67                    | 8.5                       | 86.3    |          |
| N6038-01 | RB-29-(2.5-4.5) | 28     | 1.15           | 8.83         | 9.98                    | 8.85                      | 87.2    |          |
| N6038-02 | RB-29-(8-10)    | 29     | 1.13           | 8.75         | 9.88                    | 8.79                      | 87.5    |          |
| N6038-03 | RB-30-(1.5-3.5) | 30     | 0.95           | 9.02         | 9.97                    | 8.77                      | 86.7    |          |
| N6038-04 | RB-30-(6-8)     | 31     | 1.14           | 8.66         | 9.8                     | 8.8                       | 88.5    |          |
| N6038-05 | RB-31-(1-3)     | 32     | 1.16           | 8.76         | 9.92                    | 8.7                       | 86.1    |          |
| N6038-06 | RB-31-(6.5-8.5) | 33     | 1.17           | 8.73         | 9.9                     | 9.31                      | 93.2    |          |
| N6038-07 | RB-32-(1.5-3.5) | 34     | 1.11           | 8.50         | 9.61                    | 8.98                      | 92.6    |          |
| N6038-08 | RB-32-(7-9)     | 35     | 0.96           | 9.01         | 9.97                    | 8.74                      | 86.3    |          |
| N6038-09 | RB-33-(2-4)     | 36     | 0.91           | 8.87         | 9.78                    | 8.41                      | 84.6    |          |
| N6038-10 | RB-33-(5-7)     | 37     | 0.93           | 8.96         | 9.89                    | 8.47                      | 84.2    |          |
| N6038-11 | RB-34-(1.5-2)   | 38     | 0.91           | 8.66         | 9.57                    | 8.69                      | 89.8    |          |
| N6038-12 | RB-35-(2.5-4.5) | 39     | 1.16           | 8.56         | 9.72                    | 8.53                      | 86.1    |          |
| N6038-13 | RB-35-(5-7)     | 40     | 0.92           | 9.05         | 9.97                    | 9.16                      | 91.0    |          |
| N6038-14 | RB-36-(0-2)     | 41     | 0.95           | 9.00         | 9.95                    | 8.12                      | 79.7    |          |
| N6038-15 | RB-36-(3-5)     | 42     | 0.91           | 8.66         | 9.57                    | 9.08                      | 94.3    |          |
| N6038-16 | RB-37-(0-2)     | 43     | 0.91           | 8.95         | 9.86                    | 8.54                      | 85.3    |          |
| N6038-17 | RB-37-(3-5)     | 44     | 0.91           | 8.83         | 9.74                    | 9.4                       | 96.1    |          |
| N6038-18 | RB-38-(0-2)     | 45     | 1.11           | 8.43         | 9.54                    | 8.34                      | 85.8    |          |
| N6038-19 | RB-38-(3-5)     | 46     | 0.91           | 8.73         | 9.64                    | 9.14                      | 94.3    |          |
| N6038-20 | RB-39-(0-2)     | 47     | 0.92           | 8.91         | 9.83                    | 8.03                      | 79.8    |          |
| N6038-21 | RB-39-(3-5)     | 48     | 0.91           | 8.65         | 9.56                    | 9.11                      | 94.8    |          |



PERCENT SOLID

Supervisor: Iwona  
Analyst: jignesh  
Date: 12/14/2022

OVENTEMP IN Celsius(°C): 107  
Time IN: 17:00  
In Date: 12/13/2022  
Weight Check 1.0g: 1.00  
Weight Check 10g: 10.00  
OvenID: M OVEN-1

OVENTEMP OUT Celsius(°C): 103  
Time OUT: 08:33  
Out Date: 12/14/2022  
Weight Check 1.0g: 1.00  
Weight Check 10g: 10.00  
BalanceID: M SC-4  
Thermometer ID: %SOLIDS-OVEN

QC:LB123245

| Lab ID   | Client SampleID            | Dish # | Dish Wt(g) (A) | Sample Wt(g) | Dish + Sample Wt(g) (B) | Dish+Dry Sample Wt(g) (C) | % Solid | Comments        |
|----------|----------------------------|--------|----------------|--------------|-------------------------|---------------------------|---------|-----------------|
| N6038-22 | RB-40-(0-2)                | 49     | 0.96           | 9.01         | 9.97                    | 8.19                      | 80.2    |                 |
| N6038-23 | RB-40-(3-5)                | 50     | 0.89           | 8.67         | 9.56                    | 8.74                      | 90.5    |                 |
| N6038-24 | RB-41-(0-2)                | 51     | 1.14           | 8.83         | 9.97                    | 8.74                      | 86.1    |                 |
| N6038-25 | RB-41-(3-5)                | 52     | 0.94           | 8.62         | 9.56                    | 9.15                      | 95.2    |                 |
| N6038-26 | RB-42-(0-2)                | 53     | 1.18           | 8.79         | 9.97                    | 8.36                      | 81.7    |                 |
| N6038-27 | RB-42-(3-5)                | 54     | 0.92           | 8.79         | 9.71                    | 8.79                      | 89.5    |                 |
| N6038-28 | N6038-27MS                 | 55     | 0.92           | 8.79         | 9.71                    | 8.79                      | 89.5    |                 |
| N6038-29 | N6038-27MSD                | 56     | 0.92           | 8.79         | 9.71                    | 8.79                      | 89.5    |                 |
| N6039-01 | ACA-CONCRETE-1213          | 67     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | CONCRETE SAMPLE |
| N6041-01 | SP25-11-20221213-13.0-13.5 | 57     | 0.91           | 8.70         | 9.61                    | 8.17                      | 83.4    |                 |
| N6041-02 | SP25-11-20221213-19.0-19.5 | 58     | 0.92           | 9.05         | 9.97                    | 8.44                      | 83.1    |                 |
| N6046-01 | HR-01-121322               | 68     | 0.91           | 8.76         | 9.67                    | 8.76                      | 89.6    |                 |
| N6046-02 | HR-01-121322-EPH-2         | 69     | 0.91           | 8.76         | 9.67                    | 8.76                      | 89.6    |                 |
| N6046-03 | HR-02-121322               | 70     | 0.93           | 8.84         | 9.77                    | 9.00                      | 91.3    |                 |
| N6046-04 | HR-02-121322-EPH-2         | 71     | 0.93           | 8.84         | 9.77                    | 9.00                      | 91.3    |                 |
| N6048-01 | MH-22                      | 72     | 0.91           | 9.06         | 9.97                    | 9.55                      | 95.4    |                 |
| N6048-03 | MH-22-EPH                  | 73     | 0.92           | 9.01         | 9.93                    | 9.04                      | 90.1    |                 |
| N6048-04 | TP-R                       | 74     | 0.93           | 9.05         | 9.98                    | 9.1                       | 90.3    |                 |
| N6048-06 | TP-R-EPH                   | 75     | 0.93           | 8.83         | 9.76                    | 9.03                      | 91.7    |                 |

$$\% \text{ Solid} = \frac{(C-A) * 100}{(B-A)}$$