



PERCENT SOLID

Supervisor: Iwona

Analyst: JIGNESH

Date: 7/24/2023

OVENTEMP IN Celsius(°C): 107

Time IN: 17:35

In Date: 07/21/2023

Weight Check 1.0g: 1.00

Weight Check 10g: 10.00

OvenID: M OVEN-1

OVENTEMP OUT Celsius(°C): 103

Time OUT: 08:33

Out Date: 07/22/2023

Weight Check 1.0g: 1.00

Weight Check 10g: 10.00

BalanceID: M SC-4

Thermometer ID: %SOLIDS-OVEN

QC:LB126547

| Lab ID   | Client SampleID      | Dish # | Dish Wt(g) (A) | Sample Wt(g) | Dish + Sample Wt(g) (B) | Dish+Dry Sample Wt(g) (C) | % Solid | Comments        |
|----------|----------------------|--------|----------------|--------------|-------------------------|---------------------------|---------|-----------------|
| 03686-05 | SB-20-0-2-20230720   | 1      | 1.14           | 8.84         | 9.98                    | 9.41                      | 93.6    |                 |
| 03686-06 | SB-20-2-4-20230720   | 2      | 1.16           | 8.48         | 9.64                    | 8.79                      | 90.0    |                 |
| 03686-07 | SB-18-0-2-20230720   | 3      | 1.15           | 8.40         | 9.55                    | 8.63                      | 89.0    |                 |
| 03686-08 | SB-18-16-18-20230720 | 4      | 1.11           | 8.68         | 9.79                    | 9.38                      | 95.3    |                 |
| 03697-01 | CONC-1               | 5      | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | CONCRETE SAMPLE |
| 03697-02 | CONC-2               | 6      | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | CONCRETE SAMPLE |
| 03697-03 | CONC-3               | 7      | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | CONCRETE SAMPLE |
| 03697-04 | CONC-4               | 8      | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | CONCRETE SAMPLE |
| 03698-01 | X182-S8              | 9      | 1.15           | 8.38         | 9.53                    | 8.27                      | 85.0    |                 |
| 03698-02 | X182-B8              | 10     | 1.15           | 8.83         | 9.98                    | 9.04                      | 89.4    |                 |
| 03698-03 | X182-B7              | 11     | 1.19           | 8.70         | 9.89                    | 8.98                      | 89.5    |                 |
| 03698-04 | X182-B6              | 12     | 1.19           | 8.78         | 9.97                    | 9.06                      | 89.6    |                 |
| 03698-05 | X182-S7              | 13     | 1.12           | 8.87         | 9.99                    | 8.96                      | 88.4    |                 |
| 03699-01 | 001                  | 14     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | OIL SAMPLE      |
| 03699-02 | 002                  | 15     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | OIL SAMPLE      |
| 03699-03 | 003                  | 16     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | OIL SAMPLE      |
| 03700-01 | 001                  | 17     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | OIL SAMPLE      |
| 03701-01 | 002                  | 18     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | OIL SAMPLE      |
| 03701-02 | 003                  | 19     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | OIL SAMPLE      |
| 03702-01 | 004                  | 20     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | OIL SAMPLE      |
| 03703-01 | 001                  | 21     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | OIL SAMPLE      |
| 03703-02 | 002                  | 22     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | OIL SAMPLE      |
| 03704-05 | SVOC-GPC-BLANK       | 45     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   |                 |
| 03704-06 | PEST-GPC-BLANK       | 46     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   |                 |
| 03704-07 | PEST-GPC-BLANK-SPIKE | 47     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   |                 |
| 03704-08 | PCB-GPC-BLANK        | 48     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   |                 |
| 03704-09 | PCB-GPC-BLANK-SPIKE  | 49     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   |                 |
| 03704-10 | SVOC-GPC2-BLANK      | 50     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   |                 |



PERCENT SOLID

Supervisor: Iwona

Analyst: JIGNESH

Date: 7/24/2023

OVENTEMP IN Celsius(°C): 107

Time IN: 17:35

In Date: 07/21/2023

Weight Check 1.0g: 1.00

Weight Check 10g: 10.00

OvenID: M OVEN-1

OVENTEMP OUT Celsius(°C): 103

Time OUT: 08:33

Out Date: 07/22/2023

Weight Check 1.0g: 1.00

Weight Check 10g: 10.00

BalanceID: M SC-4

Thermometer ID: %SOLIDS-OVEN

QC:LB126547

| Lab ID   | Client SampleID       | Dish # | Dish Wt(g) (A) | Sample Wt(g) | Dish + Sample Wt(g) (B) | Dish+Dry Sample Wt(g) (C) | % Solid | Comments    |
|----------|-----------------------|--------|----------------|--------------|-------------------------|---------------------------|---------|-------------|
| O3704-11 | PEST-GPC2-BLANK       | 51     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   |             |
| O3704-12 | PEST-GPC2-BLANK-SPIKE | 52     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   |             |
| O3704-13 | PCB-GCP2-BLANK        | 53     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   |             |
| O3704-14 | PCB-GCP2-BLANK-SPIKE  | 54     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   |             |
| O3705-01 | 003                   | 23     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | OIL SAMPLE  |
| O3707-01 | EO-01-072023          | 24     | 1.12           | 8.75         | 9.87                    | 9.12                      | 91.4    |             |
| O3707-02 | EO-01-072023-EPH-2    | 25     | 1.19           | 8.43         | 9.62                    | 8.63                      | 88.3    |             |
| O3708-01 | PL-02-072023          | 26     | 1.19           | 8.53         | 9.72                    | 8.83                      | 89.6    |             |
| O3708-02 | PL-02-072023-EPH-2    | 27     | 1.11           | 8.56         | 9.67                    | 9.16                      | 94.0    |             |
| O3710-01 | PIPE-1                | 64     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3710-02 | PIPE-2                | 65     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3710-03 | PIPE-3                | 66     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3710-04 | PIPE-4                | 67     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3710-05 | PIPE-5                | 68     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3710-06 | PIPE-6                | 69     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3710-07 | PIPE-7                | 70     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3710-08 | PIPE-8                | 71     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3710-09 | PIPE-9                | 72     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3710-10 | PIPE-10               | 73     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3710-11 | PIPE-11               | 74     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3710-12 | PIPE-12               | 75     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3710-13 | PIPE-13               | 76     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3710-14 | PIPE-14               | 77     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3710-15 | PIPE-15               | 78     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3710-16 | PIPE-16               | 79     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3710-17 | PIPE-17               | 80     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3710-18 | PIPE-18               | 81     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3710-19 | PIPE-20               | 82     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |



PERCENT SOLID

Supervisor: Iwona

Analyst: JIGNESH

Date: 7/24/2023

OVENTEMP IN Celsius(°C): 107

Time IN: 17:35

In Date: 07/21/2023

Weight Check 1.0g: 1.00

Weight Check 10g: 10.00

OvenID: M OVEN-1

OVENTEMP OUT Celsius(°C): 103

Time OUT: 08:33

Out Date: 07/22/2023

Weight Check 1.0g: 1.00

Weight Check 10g: 10.00

BalanceID: M SC-4

Thermometer ID: %SOLIDS-OVEN

QC:LB126547

| Lab ID   | Client SampleID | Dish # | Dish Wt(g) (A) | Sample Wt(g) | Dish + Sample Wt(g) (B) | Dish+Dry Sample Wt(g) (C) | % Solid | Comments    |
|----------|-----------------|--------|----------------|--------------|-------------------------|---------------------------|---------|-------------|
| O3710-20 | PIPE-21         | 83     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3710-21 | PIPE-22         | 84     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3710-22 | PIPE-23         | 85     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3710-23 | PIPE-24         | 86     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3710-24 | PIPE-25         | 87     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3710-25 | PIPE-26         | 88     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3710-26 | PIPE-27         | 89     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3710-27 | PIPE-28         | 90     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3710-28 | PIPE-29         | 91     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3710-29 | PIPE-30         | 92     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3710-30 | PIPE-31         | 93     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3711-01 | PIPE-32         | 94     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3711-02 | PIPE-33         | 95     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3711-03 | PIPE-34         | 96     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3711-04 | PIPE-35         | 97     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3711-05 | PIPE-36         | 98     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3711-06 | PIPE-37         | 99     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3711-07 | PIPE-38         | 100    | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3711-08 | PIPE-39         | 101    | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3711-09 | PIPE-40         | 102    | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3711-10 | PIPE-41         | 103    | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3711-11 | PIPE-42         | 104    | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3711-12 | PIPE-43         | 105    | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3711-13 | PIPE-44         | 106    | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3711-14 | PIPE-45         | 107    | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3711-15 | PIPE-46         | 108    | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3711-16 | PIPE-47         | 109    | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3711-17 | PIPE-48         | 110    | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |



PERCENT SOLID

Supervisor: Iwona

Analyst: JIGNESH

Date: 7/24/2023

OVENTEMP IN Celsius(°C): 107

Time IN: 17:35

In Date: 07/21/2023

Weight Check 1.0g: 1.00

Weight Check 10g: 10.00

OvenID: M OVEN-1

OVENTEMP OUT Celsius(°C): 103

Time OUT: 08:33

Out Date: 07/22/2023

Weight Check 1.0g: 1.00

Weight Check 10g: 10.00

BalanceID: M SC-4

Thermometer ID: %SOLIDS-OVEN

QC:LB126547

| Lab ID   | Client SampleID | Dish # | Dish Wt(g) (A) | Sample Wt(g) | Dish + Sample Wt(g) (B) | Dish+Dry Sample Wt(g) (C) | % Solid | Comments    |
|----------|-----------------|--------|----------------|--------------|-------------------------|---------------------------|---------|-------------|
| O3711-18 | PIPE-49         | 111    | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3711-19 | PIPE-50         | 112    | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3711-20 | PIPE-19         | 113    | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3715-01 | T842-FH-01-CT   | 28     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3715-02 | T842-FH-01-BW   | 29     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3715-03 | T842-FH-02-CT   | 30     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3715-04 | T842-FH-02-BW   | 31     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3715-05 | T842-FH-03-CT   | 32     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3715-06 | T842-FH-03-BW   | 33     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3715-07 | T842-FH-04-CT   | 34     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3715-08 | T842-FH-04-BW   | 35     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3715-09 | T842-CT-01      | 36     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3715-10 | T842-CT-02      | 37     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3715-11 | T843-CT-01      | 38     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3715-12 | T841-BTW-01     | 39     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3715-13 | FIELD-BLANK     | 40     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3717-01 | TP-1            | 41     | 1.15           | 8.82         | 9.97                    | 8.85                      | 87.3    |             |
| O3717-03 | TP-1-EPH-2      | 42     | 1.19           | 8.71         | 9.9                     | 8.7                       | 86.2    |             |
| O3717-04 | TP-2            | 43     | 1.15           | 8.81         | 9.96                    | 9.00                      | 89.1    |             |
| O3717-06 | TP-2-EPH-2      | 44     | 1.13           | 8.60         | 9.73                    | 8.1                       | 81.0    |             |
| O3718-01 | 34595           | 114    | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3719-01 | B-P11A          | 55     | 1.13           | 8.66         | 9.79                    | 8.71                      | 87.5    |             |
| O3719-02 | B-P11B          | 56     | 1.19           | 8.55         | 9.74                    | 8.91                      | 90.3    |             |
| O3719-03 | B-P22A          | 57     | 1.11           | 8.51         | 9.62                    | 8.47                      | 86.5    |             |
| O3719-04 | B-P22B          | 58     | 1.15           | 8.80         | 9.95                    | 8.52                      | 83.8    |             |
| O3719-05 | B-P23A          | 59     | 1.14           | 8.50         | 9.64                    | 8.53                      | 86.9    |             |
| O3719-06 | B-P23B          | 60     | 1.12           | 8.67         | 9.79                    | 8.76                      | 88.1    |             |
| O3720-01 | 34386           | 115    | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |



PERCENT SOLID

Supervisor: Iwona  
Analyst: JIGNESH  
Date: 7/24/2023

OVENTEMP IN Celsius(°C): 107  
Time IN: 17:35  
In Date: 07/21/2023  
Weight Check 1.0g: 1.00  
Weight Check 10g: 10.00  
OvenID: M OVEN-1

OVENTEMP OUT Celsius(°C): 103  
Time OUT: 08:33  
Out Date: 07/22/2023  
Weight Check 1.0g: 1.00  
Weight Check 10g: 10.00  
BalanceID: M SC-4  
Thermometer ID: %SOLIDS-OVEN

QC:LB126547

| Lab ID   | Client SampleID | Dish # | Dish Wt(g) (A) | Sample Wt(g) | Dish + Sample Wt(g) (B) | Dish+Dry Sample Wt(g) (C) | % Solid | Comments |
|----------|-----------------|--------|----------------|--------------|-------------------------|---------------------------|---------|----------|
| O3722-01 | 34339           | 116    | 1.12           | 8.59         | 9.71                    | 9.48                      | 97.3    |          |
| O3722-02 | 34340           | 117    | 1.17           | 8.60         | 9.77                    | 9.6                       | 98.0    |          |
| O3722-03 | 34339-40        | 118    | 1.15           | 8.42         | 9.57                    | 9.39                      | 97.9    |          |
| O3722-04 | 33713           | 119    | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | debris   |
| O3723-01 | S-1             | 61     | 1.18           | 8.66         | 9.84                    | 8.31                      | 82.3    |          |
| O3723-02 | S-2             | 62     | 1.16           | 8.67         | 9.83                    | 8.54                      | 85.1    |          |
| O3723-03 | S-3             | 63     | 1.12           | 8.62         | 9.74                    | 8.41                      | 84.6    |          |
| O3724-01 | 185465          | 120    | 1.18           | 8.67         | 9.85                    | 9.34                      | 94.1    |          |
| O3724-02 | 185465          | 121    | 1.14           | 8.59         | 9.73                    | 9.26                      | 94.5    |          |
| O3724-03 | 363             | 122    | 1.18           | 8.81         | 9.99                    | 9.44                      | 93.8    |          |
| O3724-04 | 363             | 123    | 1.11           | 8.86         | 9.97                    | 9.3                       | 92.4    |          |

$$\% \text{ Solid} = \frac{(C-A) * 100}{(B-A)}$$