



PERCENT SOLID

Supervisor: Iwona

Analyst: JIGNESH

Date: 7/28/2023

OVENTEMP IN Celsius(°C): 107

Time IN: 17:37

In Date: 07/27/2023

Weight Check 1.0g: 1.00

Weight Check 10g: 10.00

OvenID: M OVEN-1

OVENTEMP OUT Celsius(°C): 103

Time OUT: 08:33

Out Date: 07/28/2023

Weight Check 1.0g: 1.00

Weight Check 10g: 10.00

BalanceID: M SC-4

Thermometer ID: %SOLIDS-OVEN

QC:LB126610

| Lab ID   | Client SampleID         | Dish # | Dish Wt(g) (A) | Sample Wt(g) | Dish + Sample Wt(g) (B) | Dish+Dry Sample Wt(g) (C) | % Solid | Comments                 |
|----------|-------------------------|--------|----------------|--------------|-------------------------|---------------------------|---------|--------------------------|
| O3780-01 | ACM-2                   | 1      | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | TAR WRAP                 |
| O3780-02 | ACM-969                 | 2      | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | TAR WRAP                 |
| O3787-01 | KINGSLAND-SUB-T2        | 3      | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | STONE SAMPLE,100% SOLIDS |
| O3787-02 | KINGSLAND-SUB-T2-EPH-2  | 4      | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | STONE SAMPLE,100% SOLIDS |
| O3788-01 | CHRT-20430              | 5      | 1.12           | 8.75         | 9.87                    | 7.23                      | 69.8    |                          |
| O3788-02 | CHRT-20430-EPH-2        | 6      | 1.18           | 8.79         | 9.97                    | 6.81                      | 64.1    |                          |
| O3792-01 | KMA743R-1-1             | 7      | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | PILC REEL                |
| O3792-02 | KMA743R-1-2             | 8      | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | PILC REEL                |
| O3793-01 | D3156                   | 9      | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | debris                   |
| O3794-01 | HEF397U-1-1             | 10     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | PILC REEL                |
| O3794-02 | HEF397U-1-2             | 11     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | PILC REEL                |
| O3794-03 | BC270896-1-1            | 12     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | PILC REEL                |
| O3794-04 | BC270896-1-2            | 13     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | PILC REEL                |
| O3794-05 | KZZ065I-1-1             | 14     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | PILC REEL                |
| O3794-06 | KZZ065I-1-2             | 15     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | PILC REEL                |
| O3794-07 | BC245029-1-1            | 16     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | PILC REEL                |
| O3794-08 | BC245029-1-2            | 17     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | PILC REEL                |
| O3794-09 | KMA884V-1-1             | 18     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | PILC REEL                |
| O3794-10 | KMA884V-1-2             | 19     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | PILC REEL                |
| O3795-01 | TOPSOIL-OU3-DENALI-TEMP | 20     | 1.16           | 8.63         | 9.79                    | 9.16                      | 92.7    |                          |
| O3796-01 | TOPSOIL-OU3-DENALI-TEMP | 21     | 1.18           | 8.42         | 9.6                     | 8.74                      | 89.8    |                          |
| O3797-01 | HANOVER-ST-1            | 43     | 1.19           | 8.63         | 9.82                    | 8.51                      | 84.8    |                          |
| O3797-03 | HANOVER-ST-1-EPH-2      | 44     | 1.11           | 8.78         | 9.89                    | 8.7                       | 86.4    |                          |
| O3797-04 | HANOVER-ST-2            | 45     | 1.15           | 8.80         | 9.95                    | 8.92                      | 88.3    |                          |
| O3797-06 | HANOVER-ST-2-EPH-2      | 46     | 1.19           | 8.53         | 9.72                    | 9.34                      | 95.5    |                          |
| O3798-01 | BKG-SED-3               | 22     | 1.19           | 8.80         | 9.99                    | 8.54                      | 83.5    |                          |
| O3798-02 | BKG-SED-2               | 23     | 1.19           | 8.75         | 9.94                    | 7.77                      | 75.2    |                          |



PERCENT SOLID

Supervisor: Iwona

Analyst: JIGNESH

Date: 7/28/2023

OVENTEMP IN Celsius(°C): 107

Time IN: 17:37

In Date: 07/27/2023

Weight Check 1.0g: 1.00

Weight Check 10g: 10.00

OvenID: M OVEN-1

OVENTEMP OUT Celsius(°C): 103

Time OUT: 08:33

Out Date: 07/28/2023

Weight Check 1.0g: 1.00

Weight Check 10g: 10.00

BalanceID: M SC-4

Thermometer ID: %SOLIDS-OVEN

QC:LB126610

| Lab ID   | Client SampleID      | Dish # | Dish Wt(g) (A) | Sample Wt(g) | Dish + Sample Wt(g) (B) | Dish+Dry Sample Wt(g) (C) | % Solid | Comments    |
|----------|----------------------|--------|----------------|--------------|-------------------------|---------------------------|---------|-------------|
| O3798-03 | BKG-SB-2             | 24     | 1.11           | 8.88         | 9.99                    | 6.85                      | 64.6    |             |
| O3798-04 | BKG-SED-1            | 25     | 1.17           | 8.61         | 9.78                    | 7.43                      | 72.7    |             |
| O3798-05 | BKG-SB-1             | 26     | 1.13           | 8.77         | 9.9                     | 7.25                      | 69.8    |             |
| O3798-06 | DUP-1-072623         | 27     | 1.19           | 8.41         | 9.6                     | 8.06                      | 81.7    |             |
| O3798-07 | DUP-02-072623        | 28     | 1.14           | 8.80         | 9.94                    | 7.24                      | 69.3    |             |
| O3807-01 | ORA-1696             | 53     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3807-02 | ORA-1697             | 54     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3809-01 | 1720                 | 55     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3809-02 | 1721                 | 56     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3809-03 | 1722                 | 57     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3809-04 | 1723                 | 58     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | WIPE SAMPLE |
| O3810-01 | B-P3A                | 29     | 1.15           | 8.82         | 9.97                    | 8.86                      | 87.4    |             |
| O3810-02 | B-P3B                | 30     | 1.17           | 8.55         | 9.72                    | 8.41                      | 84.7    |             |
| O3810-03 | B-P16A               | 31     | 1.17           | 8.57         | 9.74                    | 8.51                      | 85.6    |             |
| O3810-04 | B-P16B               | 32     | 1.18           | 8.66         | 9.84                    | 8.53                      | 84.9    |             |
| O3810-05 | B-P7A                | 33     | 1.17           | 8.52         | 9.69                    | 8.56                      | 86.7    |             |
| O3810-06 | B-P7B                | 34     | 1.12           | 8.76         | 9.88                    | 8.23                      | 81.2    |             |
| O3810-07 | B-P15B               | 35     | 1.19           | 8.80         | 9.99                    | 9.44                      | 93.7    |             |
| O3810-08 | B-P1A                | 36     | 1.19           | 8.79         | 9.98                    | 9.29                      | 92.2    |             |
| O3810-09 | B-P1B                | 37     | 1.14           | 8.83         | 9.97                    | 9.24                      | 91.7    |             |
| O3810-10 | WC-01                | 38     | 1.19           | 8.80         | 9.99                    | 9.16                      | 90.6    |             |
| O3810-11 | B-P08A               | 39     | 1.15           | 8.37         | 9.52                    | 8.68                      | 90.0    |             |
| O3810-12 | B-P08B               | 40     | 1.17           | 8.68         | 9.85                    | 9.18                      | 92.3    |             |
| O3812-01 | WC-1                 | 41     | 1.19           | 8.52         | 9.71                    | 7.71                      | 76.5    |             |
| O3812-02 | WC-1-EPH-2           | 42     | 1.17           | 8.59         | 9.76                    | 7.46                      | 73.2    |             |
| O3813-01 | PLAUDERVILLE-1       | 59     | 1.16           | 8.50         | 9.66                    | 8.85                      | 90.5    |             |
| O3813-03 | PLAUDERVILLE-1-EPH-2 | 60     | 1.18           | 8.78         | 9.96                    | 9.26                      | 92.0    |             |
| O3813-04 | PLAUDERVILLE-2       | 61     | 1.18           | 8.63         | 9.81                    | 9.1                       | 91.8    |             |



PERCENT SOLID

Supervisor: Iwona  
Analyst: JIGNESH  
Date: 7/28/2023

OVENTEMP IN Celsius(°C): 107  
Time IN: 17:37  
In Date: 07/27/2023  
Weight Check 1.0g: 1.00  
Weight Check 10g: 10.00  
OvenID: M OVEN-1

OVENTEMP OUT Celsius(°C): 103  
Time OUT: 08:33  
Out Date: 07/28/2023  
Weight Check 1.0g: 1.00  
Weight Check 10g: 10.00  
BalanceID: M SC-4  
Thermometer ID: %SOLIDS-OVEN

QC:LB126610

| Lab ID   | Client SampleID      | Dish # | Dish Wt(g) (A) | Sample Wt(g) | Dish + Sample Wt(g) (B) | Dish+Dry Sample Wt(g) (C) | % Solid | Comments    |
|----------|----------------------|--------|----------------|--------------|-------------------------|---------------------------|---------|-------------|
| O3813-06 | PLAUDERVILLE-2-EPH-2 | 62     | 1.14           | 8.80         | 9.94                    | 9.24                      | 92.0    |             |
| O3813-07 | PLAUDERVILLE-3       | 63     | 1.18           | 8.79         | 9.97                    | 9.51                      | 94.8    |             |
| O3813-09 | PLAUDERVILLE-3-EPH-2 | 64     | 1.12           | 8.68         | 9.8                     | 9.18                      | 92.9    |             |
| O3814-01 | BC258709LOZ-END-1-1  | 47     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | PILC REEL   |
| O3814-02 | BC258709LOZ-END-1-2  | 48     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | PILC REEL   |
| O3814-03 | BC248151LOZ-END-1-1  | 49     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | PILC REEL   |
| O3814-04 | BC248151LOZ-END-1-2  | 50     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | PILC REEL   |
| O3814-05 | BC258730LOZ-END-1-1  | 51     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | PILC REEL   |
| O3814-06 | BC258730LOZ-END-1-2  | 52     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | PILC REEL   |
| O3818-01 | BC274770-1-1         | 65     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | PILC REEL   |
| O3818-02 | BC274770-1-2         | 66     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | PILC REEL   |
| O3818-03 | FEB433J-1-1          | 67     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | PILC REEL   |
| O3818-04 | FEB433J-1-2          | 68     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | PILC REEL   |
| O3818-05 | BC278726-1-1         | 69     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | PILC REEL   |
| O3818-06 | BC278726-1-2         | 70     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | PILC REEL   |
| O3818-07 | BC274767-1-1         | 71     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | PILC REEL   |
| O3818-08 | BC274767-1-2         | 72     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | PILC REEL   |
| O3818-09 | BC258874-1-1         | 73     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | PILC REEL   |
| O3818-10 | BC258874-1-2         | 74     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | PILC REEL   |
| O3819-01 | 368                  | 75     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | OILY DEBRIS |

$$\% \text{ Solid} = \frac{(C-A) * 100}{(B-A)}$$