



PERCENT SOLID

Supervisor: Iwona

Analyst: JIGNESH

Date: 9/14/2023

OVENTEMP IN Celsius(°C): 106

Time IN: 17:35

In Date: 09/13/2023

Weight Check 1.0g: 1.00

Weight Check 10g: 10.00

OvenID: M OVEN-1

OVENTEMP OUT Celsius(°C): 103

Time OUT: 08:00

Out Date: 09/14/2023

Weight Check 1.0g: 1.00

Weight Check 10g: 10.00

BalanceID: M SC-4

Thermometer ID: %SOLIDS-OVEN

QC:LB127272

| Lab ID    | Client SampleID    | Dish # | Dish Wt(g) (A) | Sample Wt(g) | Dish + Sample Wt(g) (B) | Dish+Dry Sample Wt(g) (C) | % Solid | Comments  |
|-----------|--------------------|--------|----------------|--------------|-------------------------|---------------------------|---------|-----------|
| O4409-01  | WC-1 (0-2) COMP    | 1      | 1.16           | 7.45         | 8.61                    | 7.51                      | 85.2    |           |
| O4409-01D | WC-1 (0-2) COMPDUP | 2      | 1.18           | 6.89         | 8.07                    | 7.18                      | 87.1    |           |
| O4409-03  | WC-1 (0-2) GRAB    | 3      | 1.16           | 8.30         | 9.46                    | 6.88                      | 68.9    |           |
| O4409-04  | WC-2 (0-2) COMP    | 4      | 1.16           | 7.79         | 8.95                    | 7.34                      | 79.3    |           |
| O4409-06  | WC-2 (0-2) GRAB    | 5      | 1.15           | 7.43         | 8.58                    | 7.52                      | 85.7    |           |
| O4409-07  | WC-3 (0-2) COMP    | 6      | 1.17           | 7.64         | 8.81                    | 7.53                      | 83.2    |           |
| O4409-09  | WC-3 (0-2) GRAB    | 7      | 1.13           | 7.08         | 8.21                    | 7.78                      | 93.9    |           |
| O4409-10  | WC-4 (0-6) COMP    | 8      | 1.17           | 8.04         | 9.21                    | 7.84                      | 83.0    |           |
| O4409-12  | WC-4 (0-6) GRAB    | 9      | 1.14           | 8.03         | 9.17                    | 6.78                      | 70.2    |           |
| O4409-13  | WC-5 (0-6) COMP    | 10     | 1.18           | 7.18         | 8.36                    | 7.47                      | 87.6    |           |
| O4409-15  | WC-5 (0-6) GRAB    | 11     | 1.13           | 8.19         | 9.32                    | 8.04                      | 84.4    |           |
| O4409-16  | WC-6 (0-6) COMP    | 12     | 1.19           | 7.59         | 8.78                    | 3.86                      | 35.2    |           |
| O4409-18  | WC-6 (0-6) GRAB    | 13     | 1.19           | 7.68         | 8.87                    | 7.75                      | 85.4    |           |
| O4412-01  | WC-1               | 14     | 1.18           | 7.52         | 8.7                     | 7.42                      | 83.0    |           |
| O4412-02  | WC-1-EPH           | 15     | 1.15           | 7.27         | 8.42                    | 7.57                      | 88.3    |           |
| O4413-01  | KMA841S-END-1-1    | 16     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | PILC REEL |
| O4413-02  | KMA841S-END-1-2    | 17     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | PILC REEL |
| O4413-03  | KMA915W-END-1-1    | 18     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | PILC REEL |
| O4413-04  | KMA915W-END-1-2    | 19     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | PILC REEL |
| O4413-05  | KMA382K-END-1-1    | 20     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | PILC REEL |
| O4413-06  | KMA382K-END-1-2    | 21     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | PILC REEL |
| O4413-07  | KMA426I-END-1-     | 22     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | PILC REEL |
| O4413-08  | KMA426I-END-1-2    | 23     | 1.00           | 1.00         | 2.00                    | 2.00                      | 100.0   | PILC REEL |
| O4423-01  | HD-01-09132023     | 24     | 1.14           | 8.50         | 9.64                    | 8.82                      | 90.4    |           |
| O4423-02  | HD-01-09132023     | 25     | 1.12           | 8.57         | 9.69                    | 8.76                      | 89.1    |           |
| O4424-01  | SU-03-09132023     | 26     | 1.18           | 8.77         | 9.95                    | 9.00                      | 89.2    |           |
| O4424-02  | SU-03-09132023     | 27     | 1.13           | 8.70         | 9.83                    | 9.02                      | 90.7    |           |
| O4432-01  | PILE-1             | 28     | 1.18           | 8.54         | 9.72                    | 8.94                      | 90.9    |           |



PERCENT SOLID

Supervisor: Iwona  
Analyst: JIGNESH  
Date: 9/14/2023

OVENTEMP IN Celsius(°C): 106  
Time IN: 17:35  
In Date: 09/13/2023  
Weight Check 1.0g: 1.00  
Weight Check 10g: 10.00  
OvenID: M OVEN-1

OVENTEMP OUT Celsius(°C): 103  
Time OUT: 08:00  
Out Date: 09/14/2023  
Weight Check 1.0g: 1.00  
Weight Check 10g: 10.00  
BalanceID: M SC-4  
Thermometer ID: %SOLIDS-OVEN

QC:LB127272

| Lab ID   | Client SampleID | Dish # | Dish Wt(g) (A) | Sample Wt(g) | Dish + Sample Wt(g) (B) | Dish+Dry Sample Wt(g) (C) | % Solid | Comments |
|----------|-----------------|--------|----------------|--------------|-------------------------|---------------------------|---------|----------|
| O4433-01 | PILE-2          | 29     | 1.13           | 8.60         | 9.73                    | 8.7                       | 88.0    |          |
| O4434-01 | DIRTY-PILE-3    | 30     | 1.13           | 8.53         | 9.66                    | 9.44                      | 97.4    |          |

$$\% \text{ Solid} = \frac{(C-A) * 100}{(B-A)}$$