

**PERCENT SOLID**

**Supervisor:** Iwona  
**Analyst:** Niha  
**Date:** 7/17/2024

**OVENTEMP IN Celsius(°C):** 106  
**Time IN:** 17:40  
**In Date:** 07/16/2024  
**Weight Check 1.0g:** 1.00  
**Weight Check 10g:** 10.00  
**OvenID:** M OVEN#1

**OVENTEMP OUT Celsius(°C):** 103  
**Time OUT:** 09:10  
**Out Date:** 07/17/2024  
**Weight Check 1.0g:** 1.00  
**Weight Check 10g:** 10.00  
**BalanceID:** M SC-4  
**Thermometer ID:** % SOLID- OVEN

QC:LB131634

| Lab ID   | Client SampleID | Dish # | Dish Wt (g) (A) | Sample Wt (g) | Dish + Sample Wt (g) (B) | Dish+Dry Sample Wt (g) (C) | % Solid | Comments    |
|----------|-----------------|--------|-----------------|---------------|--------------------------|----------------------------|---------|-------------|
| P3129-04 | RT4259          | 1      | 1.17            | 8.45          | 9.62                     | 9.6                        | 99.8    |             |
| P3247-01 | 31558           | 2      | 1.00            | 1.00          | 2.00                     | 2.00                       | 100.0   | wipe sample |
| P3247-02 | 31559           | 3      | 1.00            | 1.00          | 2.00                     | 2.00                       | 100.0   | wipe sample |
| P3247-03 | 31560           | 4      | 1.00            | 1.00          | 2.00                     | 2.00                       | 100.0   | wipe sample |
| P3251-02 | 50389           | 5      | 1.00            | 1.00          | 2.00                     | 2.00                       | 100.0   | wipe sample |
| P3251-03 | 50387           | 6      | 1.00            | 1.00          | 2.00                     | 2.00                       | 100.0   | wipe sample |
| P3253-01 | HIL029L-1-1     | 7      | 1.00            | 1.00          | 2.00                     | 2.00                       | 100.0   | oilc        |
| P3253-02 | HIL029L-1-2     | 8      | 1.00            | 1.00          | 2.00                     | 2.00                       | 100.0   | oilc        |
| P3253-03 | ECA3396-1-1     | 9      | 1.00            | 1.00          | 2.00                     | 2.00                       | 100.0   | oilc        |
| P3253-04 | ECA3396-1-2     | 10     | 1.00            | 1.00          | 2.00                     | 2.00                       | 100.0   | oilc        |
| P3253-05 | COMP-1          | 11     | 1.19            | 8.41          | 9.6                      | 9.07                       | 93.7    |             |
| P3253-06 | COMP-2          | 12     | 1.00            | 1.00          | 2.00                     | 2.00                       | 100.0   | debris      |
| P3253-07 | ELZ-24-00058    | 13     | 1.00            | 1.00          | 2.00                     | 2.00                       | 100.0   | debris      |
| P3254-01 | 72-11938        | 14     | 1.18            | 8.43          | 9.61                     | 9.05                       | 93.4    |             |
| P3254-02 | SOM-24-00068    | 15     | 1.00            | 1.00          | 2.00                     | 2.00                       | 100.0   | oil sample  |
| P3254-03 | SOM-24-00069    | 16     | 1.00            | 1.00          | 2.00                     | 2.00                       | 100.0   | debris      |
| P3254-04 | COMP-1          | 17     | 1.00            | 1.00          | 2.00                     | 2.00                       | 100.0   | debris      |
| P3254-05 | COMP-2          | 18     | 1.00            | 1.00          | 2.00                     | 2.00                       | 100.0   | debris      |
| P3255-01 | HD-01-07152024  | 19     | 1.18            | 8.53          | 9.71                     | 9.15                       | 93.4    |             |
| P3255-02 | HD-01-07152024  | 20     | 1.17            | 8.48          | 9.65                     | 9.32                       | 96.1    |             |
| P3266-01 | SP-1            | 21     | 1.17            | 8.58          | 9.75                     | 9.71                       | 99.5    |             |
| P3266-03 | SP-1-COMP       | 22     | 1.16            | 8.54          | 9.7                      | 9.68                       | 99.8    |             |
| P3266-05 | SP-2            | 23     | 1.17            | 8.78          | 9.95                     | 9.94                       | 99.9    |             |
| P3266-07 | SP-2-COMP       | 24     | 1.17            | 8.77          | 9.94                     | 9.93                       | 99.9    |             |

$$\% \text{ Solid} = \frac{(C-A) * 100}{(B-A)}$$