

Data Path : Z:\HPCHEM1\HPLC_L\Data\HL031816\
 Data File : HL006334.D
 Signal(s) : vwd1A.ch
 Acq On : 18-Mar-2016, 15:28
 Operator : UM/MA
 Sample : H1824-03
 Misc :
 ALS Vial : 6 Sample Multiplier: 1

Instrument :
 HPLC_L
 ClientSampleId :
 LOD-SOIL2016-01

Integration File: AUTOINT1.E
 Quant Time: Mar 18 17:49:39 2016
 Quant Method : Z:\HPCHEM1\HPLC_L\Methods\HL031516.M
 Quant Title :
 QLast Update : Tue Mar 15 18:28:19 2016
 Response via : Initial Calibration
 Integrator: ChemStation

Volume Inj. : 50 ul
 Signal Phase : ZORBAX Extend-C18
 Signal Info : 4.6 X 100mm 3.5-Micron 80A

Compound	R.T.	Response	Conc Units

System Monitoring Compounds			
1) S 4-Nitroaniline	2.110	1015970	571.189 ug/L m
Target Compounds			
2) T HMX	1.276	312047	62.150 ug/L
3) T RDX	2.149f	2150409	225.362 ug/L m
4) T 1,3,5-Trinitrobenzene	3.563	745177	56.910 ug/L
5) T 1,3-Dinitrobenzene	4.715	1156686	58.749 ng/ml
6) T 3,5-Dinitroaniline	5.431	931085	61.451 ug/L
7) T Nitrobenzene	6.086	707820	60.593 ug/L
8) T Tetryl	8.102	521412	68.285 ug/L
9) T 2,4,6-Trinitrotoluene	8.554	748201	59.793 ug/L
10) T 2-Amino-4,6-dinitroto...	9.747	723090	54.760 ug/L m
11) T 4-Amino-2,6-dinitroto...	10.263	442732	53.323 ug/L m
12) T 2,4-Dinitrotoluene	10.971	1096420	59.064 ug/L
13) T 2,6-Dinitrotoluene	11.304	571854	60.973 ug/L
14) T 2-Nitrotoluene	15.310	1242657	54.518 ug/L
15) T 4-Nitrotoluene	16.637	1090978	59.747 ug/L
16) T 3-Nitrotoluene	18.008	1385389	55.763 ug/L m
17) T PETN	19.036	654402	52.957 ug/L m

(f)=RT Delta > 1/2 Window

(m)=manual int.

Data Path : Z:\HPCHEM1\HPLC_L\Data\HL031816\
Data File : HL006334.D
Signal(s) : vwd1A.ch
Acq On : 18-Mar-2016, 15:28
Operator : UM/MA
Sample : H1824-03
Misc :
ALS Vial : 6 Sample Multiplier: 1

Instrument :
HPLC_L
ClientSampleId :
LOD-SOIL2016-01

Integration File: AUTOINT1.E
Quant Time: Mar 18 17:49:39 2016
Quant Method : Z:\HPCHEM1\HPLC_L\Methods\HL031516.M
Quant Title :
QLast Update : Tue Mar 15 18:28:19 2016
Response via : Initial Calibration
Integrator: ChemStation

Volume Inj. : 50 ul
Signal Phase : ZORBAX Extend-C18
Signal Info : 4.6 X 100mm 3.5-Micron 80A

