

Data Path : Z:\HPCHEM1\HPLC_L\Data\HL040315\
 Data File : HL006188.D
 Signal(s) : vwd1A.ch
 Acq On : 03-Apr-2015, 19:31
 Operator : TP/IZ
 Sample : G1614-05
 Misc :
 ALS Vial : 6 Sample Multiplier: 1

Instrument :
 HPLC_L
 ClientSampleId :
 LOD-WATER2015-01

Integration File: AUTOINT1.E
 Quant Time: Apr 06 08:20:16 2015
 Quant Method : Z:\HPCHEM1\HPLC_L\methods\HL031615.M
 Quant Title :
 QLast Update : Mon Apr 06 08:15:57 2015
 Response via : Initial Calibration
 Integrator: ChemStation

Volume Inj. : 50 ul
 Signal Phase : ZORBAX Extend-C18
 Signal Info : 4.6 X 100mm 3.5-Micron 80A

	Compound	R.T.	Response	Conc Units

System Monitoring Compounds				
1) S	4-Nitroaniline	2.250	3057572	229.054 ug/L
Target Compounds				
2) T	HMX	1.331	361900	61.776 ug/L
3) T	RDX	2.250	3057572	229.054 ug/L
4) T	1,3,5-Trinitrobenzene	3.705	709161	48.041 ug/L
5) T	1,3-Dinitrobenzene	4.902	1072272	47.096 ng/ml
6) T	3,5-Dinitroaniline	5.715	803776	44.994 ug/L
7) T	Nitrobenzene	6.314	620009	45.488 ug/L
8) T	Tetryl	8.491	342095	33.978 ug/L
9) T	2,4,6-Trinitrotoluene	8.965	814894	56.248 ug/L
10) T	2-Amino-4,6-dinitroto...	10.331	1679257	103.452 ug/L m
11) T	4-Amino-2,6-dinitroto...	10.650	598411	59.877 ug/L m
12) T	2,4-Dinitrotoluene	11.455	1078781	51.543 ug/L
13) T	2,6-Dinitrotoluene	11.822	632952	58.350 ug/L
14) T	2-Nitrotoluene	15.913	2850139	105.540 ug/L
15) T	4-Nitrotoluene	17.350	1072711	64.113 ug/L
16) T	3-Nitrotoluene	18.797	1613121	57.959 ug/L
17) T	PETN	19.500	725039	60.879 ug/L m

(f)=RT Delta > 1/2 Window

(m)=manual int.

Data Path : Z:\HPCHEM1\HPLC_L\Data\HL040315\
Data File : HL006188.D
Signal(s) : vwd1A.ch
Acq On : 03-Apr-2015, 19:31
Operator : TP/IZ
Sample : G1614-05
Misc :
ALS Vial : 6 Sample Multiplier: 1

Instrument :
HPLC_L
ClientSampleId :
LOD-WATER2015-01

Integration File: AUTOINT1.E
Quant Time: Apr 06 08:20:16 2015
Quant Method : Z:\HPCHEM1\HPLC_L\methods\HL031615.M
Quant Title :
QLast Update : Mon Apr 06 08:15:57 2015
Response via : Initial Calibration
Integrator: ChemStation

Volume Inj. : 50 ul
Signal Phase : ZORBAX Extend-C18
Signal Info : 4.6 X 100mm 3.5-Micron 80A

