

Data Path : Z:\HPCHEM1\HPLC_L\Data\HL060413\
 Data File : HL005367.D
 Signal(s) : VWD1A.CH
 Acq On : 04-Jun-2013, 18:34
 Operator : QM
 Sample : HSTDCCC0500
 Misc :
 ALS Vial : 1 Sample Multiplier: 1

Instrument :
 HPLC_L
 LabSampleId :
 HSTDCCC0500

Integration File: autoint1.e
 Quant Time: Jun 07 03:06:06 2013
 Quant Method : Z:\HPCHEM1\HPLC_L\METHODS\HL060413.M
 Quant Title :
 QLast Update : Tue Jun 04 16:52:57 2013
 Response via : Initial Calibration
 Integrator: ChemStation

Volume Inj. : 50 ul
 Signal Phase : ZORBAX Extend-C18
 Signal Info : 4.6 X 100mm 3.5-Micron 80A

	Compound	R.T.	Response	Conc Units

System Monitoring Compounds				
1) S	4-Nitroaniline	1.305	1914439	495.090 ug/L
Target Compounds				
2) T	HMX	0.879	1903064	422.804 ug/L
3) T	RDX	1.697	2368849	500.718 ug/L
4) T	1,3,5-Trinitrobenzene	2.651	5302261	469.840 ug/L
5) T	1,3-Dinitrobenzene	3.539	7659471	498.328 ng/mL
6) T	3,5-Dinitroaniline	3.911	6643743	492.035 ug/L
7) T	Nitrobenzene	4.813	4868520	493.692 ug/L
8) T	Tetryl	6.368	3644236	459.799 ug/L
9) T	2,4,6-Trinitrotoluene	6.620	5346772	470.346 ug/L
10) T	2-Amino-4,6-dinitroto...	7.149	5091186	455.154 ug/L
11) T	4-Amino-2,6-dinitroto...	7.525	3096942	508.826 ug/L
12) T	2,4-Dinitrotoluene	8.284	7140304	488.917 ug/L
13) T	2,6-Dinitrotoluene	8.707	3733712	480.118 ug/L
14) T	2-Nitrotoluene	11.944	3165021	476.395 ug/L
15) T	4-Nitrotoluene	12.693	2611888	480.994 ug/L
16) T	3-Nitrotoluene	14.001	3424067	475.383 ug/L
17) T	PETN	19.568	3889366	409.128 ug/L

(f)=RT Delta > 1/2 Window

(m)=manual int.

Data Path : Z:\HPCHEM1\HPLC_L\Data\HL060413\
Data File : HL005367.D
Signal(s) : VWD1A.CH
Acq On : 04-Jun-2013, 18:34
Operator : QM
Sample : HSTDCCC0500
Misc :
ALS Vial : 1 Sample Multiplier: 1

Instrument :
HPLC_L
LabSampleId :
HSTDCCC0500

Integration File: autoint1.e
Quant Time: Jun 07 03:06:06 2013
Quant Method : Z:\HPCHEM1\HPLC_L\METHODS\HL060413.M
Quant Title :
QLast Update : Tue Jun 04 16:52:57 2013
Response via : Initial Calibration
Integrator: ChemStation

Volume Inj. : 50 ul
Signal Phase : ZORBAX Extend-C18
Signal Info : 4.6 X 100mm 3.5-Micron 80A

