

Data Path : Z:\HPCHEM1\HPLC_L\Data\HL060513\
 Data File : HL005393.D
 Signal(s) : VWD1A.CH
 Acq On : 05-Jun-2013, 20:23
 Operator : QM
 Sample : PB70098BS
 Misc :
 ALS Vial : 21 Sample Multiplier: 1

Instrument :
 HPLC_L
 ClientSampleId :
 PB70098BS

Integration File: autoint1.e
 Quant Time: Jun 07 04:18:01 2013
 Quant Method : Z:\HPCHEM1\HPLC_L\METHODS\HL060413.M
 Quant Title :
 QLast Update : Tue Jun 04 16:52:57 2013
 Response via : Initial Calibration
 Integrator: ChemStation

Volume Inj. : 50 ul
 Signal Phase : ZORBAX Extend-C18
 Signal Info : 4.6 X 100mm 3.5-Micron 80A

	Compound	R.T.	Response	Conc Units

System Monitoring Compounds				
1) S	4-Nitroaniline	1.270	1283152	331.834 ug/L
Target Compounds				
2) T	HMX	0.858	1134785	252.115 ug/L
3) T	RDX	1.659	1359948	287.460 ug/L
4) T	1,3,5-Trinitrobenzene	2.619	2683716	237.807 ug/L
5) T	1,3-Dinitrobenzene	3.484	4087416	265.929 ng/mL
6) T	3,5-Dinitroaniline	3.829	3350870	248.165 ug/L
7) T	Nitrobenzene	4.668	2567485	260.356 ug/L
8) T	Tetryl	6.059	1222621	154.260 ug/L
9) T	2,4,6-Trinitrotoluene	6.329	2663606	234.313 ug/L
10) T	2-Amino-4,6-dinitroto...	6.832	2574402	230.153 ug/L
11) T	4-Amino-2,6-dinitroto...	7.188	1617159	265.698 ug/L
12) T	2,4-Dinitrotoluene	7.941	3784732	259.151 ug/L
13) T	2,6-Dinitrotoluene	8.335	2065511	265.604 ug/L
14) T	2-Nitrotoluene	11.462	1668725	251.175 ug/L
15) T	4-Nitrotoluene	12.172	1405645	258.857 ug/L
16) T	3-Nitrotoluene	13.400	1820374	252.733 ug/L
17) T	PETN	18.848	11838411	1245.300 ug/L

(f)=RT Delta > 1/2 Window

(m)=manual int.

Data Path : Z:\HPCHEM1\HPLC_L\Data\HL060513\
Data File : HL005393.D
Signal(s) : VWD1A.CH
Acq On : 05-Jun-2013, 20:23
Operator : QM
Sample : PB70098BS
Misc :
ALS Vial : 21 Sample Multiplier: 1

Instrument :
HPLC_L
ClientSampleID :
PB70098BS

Integration File: autoint1.e
Quant Time: Jun 07 04:18:01 2013
Quant Method : Z:\HPCHEM1\HPLC_L\METHODS\HL060413.M
Quant Title :
QLast Update : Tue Jun 04 16:52:57 2013
Response via : Initial Calibration
Integrator: ChemStation

Volume Inj. : 50 ul
Signal Phase : ZORBAX Extend-C18
Signal Info : 4.6 X 100mm 3.5-Micron 80A

