

Data Path : Z:\HPCHEM1\HPLC_N\Data\HN033115\
 Data File : HN007292.D
 Signal(s) : vwd1A.ch
 Acq On : 31-Mar-2015, 15:17
 Operator : TP/IZ
 Sample : G1614-06
 Misc :
 ALS Vial : 2 Sample Multiplier: 1

Integration File: autoint1.e
 Quant Time: Apr 02 12:31:51 2015
 Quant Method : Z:\HPCHEM1\HPLC_N\METHODS\HN031315.M
 Quant Title :
 QLast Update : Thu Apr 02 12:19:18 2015
 Response via : Initial Calibration
 Integrator: ChemStation

Volume Inj. : 50 ul
 Signal Phase : ZORBAX Extend-C18
 Signal Info : 4.6 X 100mm 3.5-Micron 80A

Compound	R.T.	Response	Conc Units
----------	------	----------	------------

System Monitoring Compounds

1) S 4-Nitroaniline	1.288	2132942	557.669 ug/L
---------------------	-------	---------	--------------

Target Compounds

2) T HMX	0.872	894712	195.139 ug/L
3) T RDX	1.677	1111163	199.886 ug/L
4) T 1,3,5-Trinitrobenzene	2.637	2236780	199.459 ug/L
5) T 1,3-Dinitrobenzene	3.499	3542800	209.858 ng/ml
6) T 3,5-Dinitroaniline	3.858	2799436	208.857 ug/L
7) T Nitrobenzene	4.735	2040779	204.808 ug/L
8) T Tetryl	6.253	1138757	141.525 ug/L
9) T 2,4,6-Trinitrotoluene	6.486	2120759	190.792 ug/L
10) T 2-Amino-4,6-dinitroto...	7.004	2130313	191.893 ug/L
11) T 4-Amino-2,6-dinitroto...	7.377	1406910	201.091 ug/L
12) T 2,4-Dinitrotoluene	8.133	3137344	206.848 ug/L
13) T 2,6-Dinitrotoluene	8.545	1694790	201.083 ug/L
14) T 2-Nitrotoluene	11.849	1312591	192.505 ug/L
15) T 4-Nitrotoluene	12.556	989842	153.966 ug/L
16) T 3-Nitrotoluene	13.869	1405337	208.940 ug/L
17) T PETN	19.186	2076445	212.771 ug/L


(f)=RT Delta > 1/2 Window

(m)=manual int.

Data Path : Z:\HPCHEM1\HPLC_NData\HN033115\
Data File : HN007292.D
Signal(s) : vwd1A.ch
Acq On : 31-Mar-2015, 15:17
Operator : TP/IZ
Sample : G1614-06
Misc :
ALS Vial : 2 Sample Multiplier: 1

Integration File: autoint1.e
Quant Time: Apr 02 12:31:51 2015
Quant Method : Z:\HPCHEM1\HPLC_NMETHODS\HN031315.M
Quant Title :
QLast Update : Thu Apr 02 12:19:18 2015
Response via : Initial Calibration
Integrator: ChemStation

Volume Inj. : 50 ul
Signal Phase : ZORBAX Extend-C18
Signal Info : 4.6 X 100mm 3.5-Micron 80A



The printer must be in Portrait mode.