

Data Path : Z:\HPCHEM1\HPLC_N\Data\HN042814\
 Data File : HN005952.D
 Signal(s) : VWD1A.CH
 Acq On : 28-Apr-2014, 19:11
 Operator : HNP
 Sample : HSTDICC0100
 Misc :
 ALS Vial : 5 Sample Multiplier: 1

Instrument :
 HPLC_N
 LabSampleId :
 HSTDICC0100

Integration File: autoint1.e
 Quant Time: Apr 29 16:47:13 2014
 Quant Method : Z:\HPCHEM1\HPLC_N\METHODS\HN042814.M
 Quant Title :
 QLast Update : Tue Apr 29 08:43:22 2014
 Response via : Initial Calibration
 Integrator: ChemStation

Volume Inj. : 50 ul
 Signal Phase : ZORBAX Extend-C18
 Signal Info : 4.6 X 100mm 3.5-Micron 80A

	Compound	R.T.	Response	Conc Units

System Monitoring Compounds				
1) S	4-Nitroaniline	1.384	393018	83.138 ug/L
Target Compounds				
2) T	HMX	0.915	668187	144.986 ug/L m
3) T	RDX	1.777	608971	120.352 ug/L m
4) T	1,3,5-Trinitrobenzene	2.811	1289362	120.578 ug/L
5) T	1,3-Dinitrobenzene	3.720	1825026	109.086 ng/mlm
6) T	3,5-Dinitroaniline	4.104	1388939	94.417 ug/L
7) T	Nitrobenzene	4.982	1065649	106.179 ug/L m
8) T	Tetryl	6.742	878390	117.493 ug/L
9) T	2,4,6-Trinitrotoluene	7.005	1285951	128.439 ug/L
10) T	2-Amino-4,6-dinitroto...	7.525	1330817	122.018 ug/L
11) T	4-Amino-2,6-dinitroto...	7.940	797457	118.190 ug/L
12) T	2,4-Dinitrotoluene	8.746	1752902	118.160 ug/L m
13) T	2,6-Dinitrotoluene	9.193	920497	111.927 ug/L
14) T	2-Nitrotoluene	12.610	651205	103.574 ug/L m
15) T	4-Nitrotoluene	13.440	617149	123.345 ug/L m
16) T	3-Nitrotoluene	14.841	2611496	135.864 ug/L m
17) T	PETN	20.562	1013206	109.714 ug/L m

(f)=RT Delta > 1/2 Window

(m)=manual int.

Data Path : Z:\HPCHEM1\HPLC_N\Data\HN042814\
Data File : HN005952.D
Signal(s) : VWD1A.CH
Acq On : 28-Apr-2014, 19:11
Operator : HNP
Sample : HSTDICC0100
Misc :
ALS Vial : 5 Sample Multiplier: 1

Instrument :
HPLC_N
LabSampleId :
HSTDICC0100

Integration File: autoint1.e
Quant Time: Apr 29 16:47:13 2014
Quant Method : Z:\HPCHEM1\HPLC_N\METHODS\HN042814.M
Quant Title :
QLast Update : Tue Apr 29 08:43:22 2014
Response via : Initial Calibration
Integrator: ChemStation

Volume Inj. : 50 ul
Signal Phase : ZORBAX Extend-C18
Signal Info : 4.6 X 100mm 3.5-Micron 80A

