

Data Path : Z:\HPCHEM1\HPLC_N\Data\HN042814\
 Data File : HN005955.D
 Signal(s) : VWD1A.CH
 Acq On : 28-Apr-2014, 20:33
 Operator : HNP
 Sample : HSTDCCC0500
 Misc :
 ALS Vial : 4 Sample Multiplier: 1

Instrument :
 HPLC_N
 LabSampleId :
 HSTDCCC0500

Integration File: autoint1.e
 Quant Time: Apr 29 16:45:07 2014
 Quant Method : Z:\HPCHEM1\HPLC_N\METHODS\HN042814.M
 Quant Title :
 QLast Update : Tue Apr 29 09:06:37 2014
 Response via : Initial Calibration
 Integrator: ChemStation

Volume Inj. : 50 ul
 Signal Phase : ZORBAX Extend-C18
 Signal Info : 4.6 X 100mm 3.5-Micron 80A

Compound	R.T.	Response	Conc Units

System Monitoring Compounds			
1) S 4-Nitroaniline	1.384	2396804	576.390 ug/L
Target Compounds			
2) T HMX	0.915	2298277	450.303 ug/L m
3) T RDX	1.784	2530385	429.871 ug/L m
4) T 1,3,5-Trinitrobenzene	2.815	5415760	457.220 ug/L
5) T 1,3-Dinitrobenzene	3.726	8555657	473.688 ng/ml
6) T 3,5-Dinitroaniline	4.110	7578862	556.446 ug/L
7) T Nitrobenzene	4.987	5256818	483.707 ug/L
8) T Tetryl	6.739	3883897	476.061 ug/L
9) T 2,4,6-Trinitrotoluene	6.994	5290688	435.259 ug/L
10) T 2-Amino-4,6-dinitroto...	7.514	5545959	449.410 ug/L
11) T 4-Amino-2,6-dinitroto...	7.918	3393964	486.746 ug/L
12) T 2,4-Dinitrotoluene	8.718	7750106	454.658 ug/L
13) T 2,6-Dinitrotoluene	9.158	4125824	472.571 ug/L
14) T 2-Nitrotoluene	12.551	3247049	490.977 ug/L
15) T 4-Nitrotoluene	13.364	2502010	475.060 ug/L
16) T 3-Nitrotoluene	14.727	9865276	459.526 ug/L
17) T PETN	20.409	5019054	562.927 ug/L m

(f)=RT Delta > 1/2 Window

(m)=manual int.

Data Path : Z:\HPCHEM1\HPLC_N\Data\HN042814\
Data File : HN005955.D
Signal(s) : VWD1A.CH
Acq On : 28-Apr-2014, 20:33
Operator : HNP
Sample : HSTDCCC0500
Misc :
ALS Vial : 4 Sample Multiplier: 1

Instrument :
HPLC_N
LabSampleId :
HSTDCCC0500

Integration File: autoint1.e
Quant Time: Apr 29 16:45:07 2014
Quant Method : Z:\HPCHEM1\HPLC_N\METHODS\HN042814.M
Quant Title :
QLast Update : Tue Apr 29 09:06:37 2014
Response via : Initial Calibration
Integrator: ChemStation

Volume Inj. : 50 ul
Signal Phase : ZORBAX Extend-C18
Signal Info : 4.6 X 100mm 3.5-Micron 80A

