

Data Path : Z:\HPCHEM1\HPLC_N\Data\HN042814\
 Data File : HN005971.D
 Signal(s) : VWD1A.CH
 Acq On : 29-Apr-2014, 03:46
 Operator : HNP
 Sample : PB76115BS
 Misc :
 ALS Vial : 22 Sample Multiplier: 1

Instrument :
 HPLC_N
 ClientSampleId :
 PB76115BS

Integration File: autoint1.e
 Quant Time: Apr 29 16:47:51 2014
 Quant Method : Z:\HPCHEM1\HPLC_N\METHODS\HN042814.M
 Quant Title :
 QLast Update : Tue Apr 29 09:06:37 2014
 Response via : Initial Calibration
 Integrator: ChemStation

Volume Inj. : 50 ul
 Signal Phase : ZORBAX Extend-C18
 Signal Info : 4.6 X 100mm 3.5-Micron 80A

Compound	R.T.	Response	Conc Units

System Monitoring Compounds			
1) S 4-Nitroaniline	1.390	735773	176.941 ug/L
Target Compounds			
2) T HMX	0.918	558324	109.393 ug/L m
3) T RDX	1.788	782712	132.970 ug/L
4) T 1,3,5-Trinitrobenzene	2.827	1381859	116.662 ug/L
5) T 1,3-Dinitrobenzene	3.747	2215471	122.661 ng/ml
6) T 3,5-Dinitroaniline	4.136	1872203	137.459 ug/L
7) T Nitrobenzene	5.019	1385297	127.468 ug/L
8) T Tetryl	6.802	799481	97.995 ug/L
9) T 2,4,6-Trinitrotoluene	7.048	1450410	119.324 ug/L
10) T 2-Amino-4,6-dinitroto...	7.578	1327970	107.610 ug/L
11) T 4-Amino-2,6-dinitroto...	7.991	914117	131.098 ug/L
12) T 2,4-Dinitrotoluene	8.781	1891167	110.945 ug/L
13) T 2,6-Dinitrotoluene	9.227	991627	113.581 ug/L
14) T 2-Nitrotoluene	12.644	821245	124.178 ug/L m
15) T 4-Nitrotoluene	13.461	616935	117.138 ug/L m
16) T 3-Nitrotoluene	14.817	2826908	131.678 ug/L m
17) T PETN	20.535	1401928	157.237 ug/L m

(f)=RT Delta > 1/2 Window

(m)=manual int.

Data Path : Z:\HPCHEM1\HPLC_N\Data\HN042814\
Data File : HN005971.D
Signal(s) : VWD1A.CH
Acq On : 29-Apr-2014, 03:46
Operator : HNP
Sample : PB76115BS
Misc :
ALS Vial : 22 Sample Multiplier: 1

Instrument :
HPLC_N
ClientSampleId :
PB76115BS

Integration File: autoint1.e
Quant Time: Apr 29 16:47:51 2014
Quant Method : Z:\HPCHEM1\HPLC_N\METHODS\HN042814.M
Quant Title :
QLast Update : Tue Apr 29 09:06:37 2014
Response via : Initial Calibration
Integrator: ChemStation

Volume Inj. : 50 ul
Signal Phase : ZORBAX Extend-C18
Signal Info : 4.6 X 100mm 3.5-Micron 80A

