

Data Path : Z:\HPCHEM1\HPLC_N\Data\HN051716\
 Data File : HN007713.D
 Signal(s) : vwd1A.ch
 Acq On : 17-May-2016, 12:53
 Operator : UM/MA
 Sample : HSTDICCC0500
 Misc :
 ALS Vial : 4 Sample Multiplier: 1

Instrument :
 HPLC_N
 ClientSampleId :
 HSTDICCC0500

Integration File: autoint1.e
 Quant Time: May 17 13:50:46 2016
 Quant Method : Z:\HPCHEM1\HPLC_N\Methods\HN051716.M
 Quant Title :
 QLast Update : Tue May 17 13:50:18 2016
 Response via : Initial Calibration
 Integrator: ChemStation

Volume Inj. : 50 ul
 Signal Phase : ZORBAX Extend-C18
 Signal Info : 4.6 X 100mm 3.5-Micron 80A

Compound	R.T.	Response	Conc Units

System Monitoring Compounds			
1) S 4-Nitroaniline	1.340	2013795	500.000 ug/L
Target Compounds			
2) T HMX	0.905	2055517	500.000 ug/L
3) T RDX	1.729	2873193	500.000 ug/L
4) T 1,3,5-Trinitrobenzene	2.669	5427946	500.000 ug/L
5) T 1,3-Dinitrobenzene	3.552	8586055	500.000 ng/ml
6) T 3,5-Dinitroaniline	3.949	6865287	500.000 ug/L
7) T Nitrobenzene	4.738	5051368	500.000 ug/L
8) T Tetryl	6.280	3873302	500.000 ug/L
9) T 2,4,6-Trinitrotoluene	6.506	5663639	500.000 ug/L
10) T 2-Amino-4,6-dinitroto...	7.115	5587726	500.000 ug/L
11) T 4-Amino-2,6-dinitroto...	7.465	3638466	500.000 ug/L
12) T 2,4-Dinitrotoluene	8.158	7817431	500.000 ug/L
13) T 2,6-Dinitrotoluene	8.554	4197180	500.000 ug/L
14) T 2-Nitrotoluene	11.698	3355874	500.000 ug/L
15) T 4-Nitrotoluene	12.437	2695113	500.000 ug/L
16) T 3-Nitrotoluene	13.699	3471775	500.000 ug/L
17) T PETN	18.809	4460567	500.000 ug/L

(f)=RT Delta > 1/2 Window

(m)=manual int.

Data Path : Z:\HPCHEM1\HPLC_N\Data\HN051716\
Data File : HN007713.D
Signal(s) : vwd1A.ch
Acq On : 17-May-2016, 12:53
Operator : UM/MA
Sample : HSTDICCC0500
Misc :
ALS Vial : 4 Sample Multiplier: 1

Instrument :
HPLC_N
ClientSampleId :
HSTDICCC0500

Integration File: autoint1.e
Quant Time: May 17 13:50:46 2016
Quant Method : Z:\HPCHEM1\HPLC_N\Methods\HN051716.M
Quant Title :
QLast Update : Tue May 17 13:50:18 2016
Response via : Initial Calibration
Integrator: ChemStation

Volume Inj. : 50 ul
Signal Phase : ZORBAX Extend-C18
Signal Info : 4.6 X 100mm 3.5-Micron 80A

