

Data Path : Z:\HPCHEM1\HPLC_N\Data\HN052015\
 Data File : HN007365.D
 Signal(s) : vwd1A.ch
 Acq On : 20-May-2015, 19:26
 Operator : TP/IZ
 Sample : HSTDICC0100
 Misc :
 ALS Vial : 6 Sample Multiplier: 1

Instrument :
 HPLC_N
 ClientSampleId :
 HSTDICC0100

Integration File: autoint1.e
 Quant Time: May 21 03:52:24 2015
 Quant Method : Z:\HPCHEM1\HPLC_N\Methods\HN052015.M
 Quant Title :
 QLast Update : Thu May 21 02:13:55 2015
 Response via : Initial Calibration
 Integrator: ChemStation

Volume Inj. : 50 ul
 Signal Phase : ZORBAX Extend-C18
 Signal Info : 4.6 X 100mm 3.5-Micron 80A

	Compound	R.T.	Response	Conc Units

System Monitoring Compounds				
1) S	4-Nitroaniline	1.333	473810	105.602 ug/L
Target Compounds				
2) T	HMX	0.890	471221	106.055 ug/L
3) T	RDX	1.710	616958	112.485 ug/L
4) T	1,3,5-Trinitrobenzene	2.656	1199778	111.248 ug/L
5) T	1,3-Dinitrobenzene	3.526	1794413	111.503 ng/ml
6) T	3,5-Dinitroaniline	3.914	1481844	114.746 ug/L
7) T	Nitrobenzene	4.713	1096963	133.579 ug/L
8) T	Tetryl	6.257	820556	144.868 ug/L
9) T	2,4,6-Trinitrotoluene	6.498	1203820	98.914 ug/L
10) T	2-Amino-4,6-dinitroto...	7.077	1173299	112.469 ug/L
11) T	4-Amino-2,6-dinitroto...	7.424	999897	126.545 ug/L m
12) T	2,4-Dinitrotoluene	8.134	3747797	244.029 ug/L
13) T	2,6-Dinitrotoluene	8.506	2258551	250.999 ug/L
14) T	2-Nitrotoluene	11.666	709633	145.043 ug/L
15) T	4-Nitrotoluene	12.455	603841	144.068 ug/L
16) T	3-Nitrotoluene	13.689	748710	149.929 ug/L
17) T	PETN	18.694	1196491	136.078 ug/L

(f)=RT Delta > 1/2 Window

(m)=manual int.

Data Path : Z:\HPCHEM1\HPLC_N\Data\HN052015\
Data File : HN007365.D
Signal(s) : vwd1A.ch
Acq On : 20-May-2015, 19:26
Operator : TP/IZ
Sample : HSTDICC0100
Misc :
ALS Vial : 6 Sample Multiplier: 1

Instrument :
HPLC_N
ClientSampleId :
HSTDICC0100

Integration File: autoint1.e
Quant Time: May 21 03:52:24 2015
Quant Method : Z:\HPCHEM1\HPLC_N\Methods\HN052015.M
Quant Title :
QLast Update : Thu May 21 02:13:55 2015
Response via : Initial Calibration
Integrator: ChemStation

Volume Inj. : 50 ul
Signal Phase : ZORBAX Extend-C18
Signal Info : 4.6 X 100mm 3.5-Micron 80A

