

Data Path : Z:\HPCHEM1\HPLC_N\Data\HN052015\
 Data File : HN007368.D
 Signal(s) : vwd1A.ch
 Acq On : 20-May-2015, 20:50
 Operator : TP/IZ
 Sample : PB83179BS
 Misc :
 ALS Vial : 9 Sample Multiplier: 1

Instrument :
 HPLC_N
 ClientSampleId :
 PB83179BS

Integration File: autoint1.e
 Quant Time: May 21 13:53:04 2015
 Quant Method : Z:\HPCHEM1\HPLC_N\Methods\HN052015.M
 Quant Title :
 QLast Update : Thu May 21 13:50:13 2015
 Response via : Initial Calibration
 Integrator: ChemStation

Volume Inj. : 50 ul
 Signal Phase : ZORBAX Extend-C18
 Signal Info : 4.6 X 100mm 3.5-Micron 80A

	Compound	R.T.	Response	Conc Units

System Monitoring Compounds				
1) S	4-Nitroaniline	1.341	2172785	480.996 ug/L
Target Compounds				
2) T	HMX	0.897	2343204	523.381 ug/L
3) T	RDX	1.723	2780572	495.437 ug/L
4) T	1,3,5-Trinitrobenzene	2.674	5530324	495.176 ug/L
5) T	1,3-Dinitrobenzene	3.549	8864462	521.025 ng/ml
6) T	3,5-Dinitroaniline	3.942	6620191	489.965 ug/L
7) T	Nitrobenzene	4.736	5164298	504.870 ug/L
8) T	Tetryl	6.279	3852024	476.818 ug/L
9) T	2,4,6-Trinitrotoluene	6.520	5785077	504.324 ug/L
10) T	2-Amino-4,6-dinitroto...	7.093	5611401	497.800 ug/L
11) T	4-Amino-2,6-dinitroto...	7.436	4157024	514.113 ug/L
12) T	2,4-Dinitrotoluene	8.150	8212644	422.121 ug/L
13) T	2,6-Dinitrotoluene	8.542	4844387	423.648 ug/L
14) T	2-Nitrotoluene	11.700	3377099	505.404 ug/L
15) T	4-Nitrotoluene	12.444	2765568	500.093 ug/L
16) T	3-Nitrotoluene	13.707	3545715	502.020 ug/L
17) T	PETN	18.684	4168468	438.652 ug/L

(f)=RT Delta > 1/2 Window

(m)=manual int.

Data Path : Z:\HPCHEM1\HPLC_N\Data\HN052015\
Data File : HN007368.D
Signal(s) : vwd1A.ch
Acq On : 20-May-2015, 20:50
Operator : TP/IZ
Sample : PB83179BS
Misc :
ALS Vial : 9 Sample Multiplier: 1

Instrument :
HPLC_N
ClientSampleId :
PB83179BS

Integration File: autoint1.e
Quant Time: May 21 13:53:04 2015
Quant Method : Z:\HPCHEM1\HPLC_N\Methods\HN052015.M
Quant Title :
QLast Update : Thu May 21 13:50:13 2015
Response via : Initial Calibration
Integrator: ChemStation

Volume Inj. : 50 ul
Signal Phase : ZORBAX Extend-C18
Signal Info : 4.6 X 100mm 3.5-Micron 80A

