

Data Path : Z:\HPCHEM1\HPLC_N\Data\HN060913\
 Data File : HN005437.D
 Signal(s) : VWD1A.CH
 Acq On : 09-Jun-2013, 14:40
 Operator : QM
 Sample : HSTDICC1000
 Misc :
 ALS Vial : 23 Sample Multiplier: 1

Instrument :
 HPLC_N
 LabSampleId :
 HSTDICC1000

Integration File: autoint1.e
 Quant Time: Jun 10 09:52:13 2013
 Quant Method : Z:\HPCHEM1\HPLC_N\METHOD\HN060913.M
 Quant Title :
 QLast Update : Sun Jun 09 12:23:56 2013
 Response via : Initial Calibration
 Integrator: ChemStation

Volume Inj. : 50 ul
 Signal Phase : ZORBAX Extend-C18
 Signal Info : 4.6 X 100mm 3.5-Micron 80A

Compound	R.T.	Response	Conc	Units

System Monitoring Compounds				
1) S 4-Nitroaniline	5.958	11449822	2693.919	ug/L
Target Compounds				
2) T HMX	4.382	11635347	2734.938	ug/L
3) T RDX	7.074	13648742	2653.600	ug/L
4) T 1,3,5-Trinitrobenzene	9.639	25052779	2284.594	ug/L
5) T 3,5-Dinitroaniline	12.427	38800045	2979.339	ng/mL
6) T 1,3-Dinitrobenzene	12.619	25802559	1657.450	ug/L
7) T Tetryl	13.219	21832539	2345.616	ug/L
8) T Nitrobenzene	14.520	24177162	4025.347	ug/L
9) T 2,4,6-Trinitrotoluene	15.913	25411486	2173.755	ug/L
10) T 4-Amino-2,6-dinitroto...	16.306	17704950	1658.188	ug/L
11) T 2-Amino-4,6-dinitroto...	17.088	29003988	4749.663	ug/L
12) T 2,6-Dinitrotoluene	19.577	17520594	1204.497	ug/L
13) T 2,4-Dinitrotoluene	20.175	43500009	5272.639	ug/L
14) T 2-Nitrotoluene	24.534	14631031	2345.909	ug/L
15) T 4-Nitrotoluene	26.406	14401084	2745.456	ug/L
16) T 3-Nitrotoluene	28.561	16621770	2502.625	ug/L

(f)=RT Delta > 1/2 Window

(m)=manual int.

Data Path : Z:\HPCHEM1\HPLC_N\Data\HN060913\
Data File : HN005437.D
Signal(s) : VWD1A.CH
Acq On : 09-Jun-2013, 14:40
Operator : QM
Sample : HSTDICC1000
Misc :
ALS Vial : 23 Sample Multiplier: 1

Instrument :
HPLC_N
LabSampleId :
HSTDICC1000

Integration File: autoint1.e
Quant Time: Jun 10 09:52:13 2013
Quant Method : Z:\HPCHEM1\HPLC_N\METHOD\HN060913.M
Quant Title :
QLast Update : Sun Jun 09 12:23:56 2013
Response via : Initial Calibration
Integrator: ChemStation

Volume Inj. : 50 ul
Signal Phase : ZORBAX Extend-C18
Signal Info : 4.6 X 100mm 3.5-Micron 80A

