

Data File : S:\HPCHEM1\HPLC_N\DATA\HN071714\HN006138.D Vial: 13
 Acq On : 17-Jul-2014, 13:59 Operator: HNP
 Sample : HSTDICC0020 Inst : G1314A
 Misc : Multiplr: 1.00
 IntFile : autoint1.e
 Quant Time: Jul 17 13:50 2014 Quant Results File: HN071714.RES

Instrument :
 HPLC_N
 ClientSampleId :
 HSTDICC0020

Manual Integrations
 APPROVED

mohammad
 7/24/2014 3:16:33 PM

Quant Method : Z:\HPCHEM1\HPLC_N\METHODS\HN071714.M
 Title :
 Last Update : Thu Jul 17 12:40:22 2014
 Response via : Initial Calibration
 DataAcq Meth : 8330AGIP.M

Volume Inj. : 50 ul
 Signal Phase : ZORBAX Extend-C18
 Signal Info : 4.6 X 100mm 3.5-Micron 80A

Compound	R.T.	Response	Conc Units

System Monitoring Compounds			
1) S 4-Nitroaniline	1.31	33467	7.599 ug/L m
Target Compounds			
2) T HMX	0.82	47120	9.606 ug/L m
4) T 1,3,5-Trinitrobenzene	2.72	70407	6.378 ug/L m
5) T 1,3-Dinitrobenzene	3.63	149752	8.919 ng/mlm
6) T 3,5-Dinitroaniline	3.98	114645	8.507 ug/L m
7) T Nitrobenzene	4.89	74255	7.218 ug/L m
8) T Tetryl	6.44	61259	7.881 ug/L m
9) T 2,4,6-Trinitrotoluene	6.78	66466	6.283 ug/L m
10) T 2-Amino-4,6-dinitrotoluene	7.22	63705	5.588 ug/L m

 Analyst Signature:_____ Analyst Name:_____ Date:_____

-----REASONS FOR MANUAL INTEGRATIONS-----

___Poor resolution of peaks exhibited on chromatogram.Compound #:_____

___Peak Integrated by software incorrectly.Compound #:_____

___OTHER:_____Compound #:_____

(f)=RT Delta > 1/2 Window (m)=manual int.

HN006138.D HN071714.M

Wed Aug 13 18:31:31 2014

RPT1

Quantitation Report

Data File : S:\HPCHEM1\HPLC_N\DATA\HN071714\HN006138.D Vial: 13
Acq On : 17-Jul-2014, 13:59 Operator: HNP
Sample : HSTDICC0020 Inst : G1314A
Misc : Multiplr: 1.00
IntFile : autoint1.e
Quant Time: Jul 17 13:50 2014 Quant Results File: HN071714.RES

Instrument :
HPLC_N
ClientSampleId :
HSTDICC0020

Manual Integrations
APPROVED

mohammad
7/24/2014 3:16:33 PM

Quant Method : Z:\HPCHEM1\HPLC_N\METHODS\HN071714.M
Title :
Last Update : Thu Jul 17 12:40:22 2014
Response via : Multiple Level Calibration
DataAcq Meth : 8330AGIP.M

Volume Inj. : 50 ul
Signal Phase : ZORBAX Extend-C18
Signal Info : 4.6 X 100mm 3.5-Micron 80A

