

Data Path : Z:\HPCHEM1\HPLC_N\Data\HN092716\
 Data File : HN007739.D
 Signal(s) : vwd1A.ch
 Acq On : 27-Sep-2016, 13:45
 Operator : UM/MA
 Sample : HSTDICCC0500
 Misc :
 ALS Vial : 4 Sample Multiplier: 1

Instrument :
 HPLC_N
 ClientSampleId :
 HSTDICCC0500

Integration File: autoint1.e
 Quant Time: Sep 27 15:54:42 2016
 Quant Method : Z:\HPCHEM1\HPLC_N\Methods\HN092716.M
 Quant Title :
 QLast Update : Tue Sep 27 15:54:27 2016
 Response via : Initial Calibration
 Integrator: ChemStation

Volume Inj. : 50 ul
 Signal Phase : ZORBAX Extend-C18
 Signal Info : 4.6 X 100mm 3.5-Micron 80A

Compound	R.T.	Response	Conc Units

System Monitoring Compounds			
1) S 4-Nitroaniline	1.325	2010417	500.000 ug/L
Target Compounds			
2) T HMX	0.892	2119078	500.000 ug/L
3) T RDX	1.684	2750636	500.000 ug/L
4) T 1,3,5-Trinitrobenzene	2.641	5294732	500.000 ug/L
5) T 1,3-Dinitrobenzene	3.515	8273614	500.000 ng/ml
6) T 3,5-Dinitroaniline	3.910	6588873	500.000 ug/L
7) T Nitrobenzene	4.695	4853582	500.000 ug/L
8) T Tetryl	6.231	3973981	500.000 ug/L
9) T 2,4,6-Trinitrotoluene	6.451	5286376	500.000 ug/L
10) T 2-Amino-4,6-dinitroto...	7.053	5407385	500.000 ug/L
11) T 4-Amino-2,6-dinitroto...	7.401	3544870	500.000 ug/L
12) T 2,4-Dinitrotoluene	8.087	7605796	500.000 ug/L
13) T 2,6-Dinitrotoluene	8.483	4160936	500.000 ug/L
14) T 2-Nitrotoluene	11.618	3285107	500.000 ug/L
15) T 4-Nitrotoluene	12.352	2845622	500.000 ug/L
16) T 3-Nitrotoluene	13.617	3637320	500.000 ug/L
17) T PETN	18.678	4211083	500.000 ug/L

(f)=RT Delta > 1/2 Window

(m)=manual int.

Data Path : Z:\HPCHEM1\HPLC_N\Data\HN092716\
Data File : HN007739.D
Signal(s) : vwd1A.ch
Acq On : 27-Sep-2016, 13:45
Operator : UM/MA
Sample : HSTDICCC0500
Misc :
ALS Vial : 4 Sample Multiplier: 1

Instrument :
HPLC_N
ClientSampleId :
HSTDICCC0500

Integration File: autoint1.e
Quant Time: Sep 27 15:54:42 2016
Quant Method : Z:\HPCHEM1\HPLC_N\Methods\HN092716.M
Quant Title :
QLast Update : Tue Sep 27 15:54:27 2016
Response via : Initial Calibration
Integrator: ChemStation

Volume Inj. : 50 ul
Signal Phase : ZORBAX Extend-C18
Signal Info : 4.6 X 100mm 3.5-Micron 80A

