

Data Path : Z:\HPCHEM1\HPLC_N\Data\HN100515\
 Data File : HN007557.D
 Signal(s) : vwd1A.ch
 Acq On : 05-Oct-2015, 15:26
 Operator : UM/MA
 Sample : G3697-01
 Misc :
 ALS Vial : 9 Sample Multiplier: 1

Instrument :
 HPLC_N
 ClientSampleId :
 38155-041515

Manual Integrations
 APPROVED

MMDadoda
 10/7/2015 4:00:17 PM

Integration File: autoint1.e
 Quant Time: Oct 05 16:51:29 2015
 Quant Method : Z:\HPCHEM1\HPLC_N\Methods\HN100515.M
 Quant Title :
 QLast Update : Mon Oct 05 14:10:20 2015
 Response via : Initial Calibration
 Integrator: ChemStation

Volume Inj. : 50 ul
 Signal Phase : ZORBAX Extend-C18
 Signal Info : 4.6 X 100mm 3.5-Micron 80A

Compound	R.T.	Response	Conc Units

System Monitoring Compounds			
1) S 4-Nitroaniline	1.324	1726577	449.480 ug/L
Target Compounds			
2) T HMX	0.892	4069799	827.401 ug/L
3) T RDX	1.710	3876000	683.233 ug/L
4) T 1,3,5-Trinitrobenzene	2.643	19092890	1624.190 ug/L
5) T 1,3-Dinitrobenzene	3.515	35751075	2110.809 ng/ml
7) T Nitrobenzene	4.688	24531519	2419.042 ug/L
9) T 2,4,6-Trinitrotoluene	6.458	11849450	984.165 ug/L
10) T 2-Amino-4,6-dinitroto...	7.050	33302807	2952.540 ug/L
11) T 4-Amino-2,6-dinitroto...	7.398	10662577	1497.726 ug/L m
13) T 2,6-Dinitrotoluene	8.478	15602369	1796.535 ug/L m
14) T 2-Nitrotoluene	11.596	10914864	1707.272 ug/L
15) T 4-Nitrotoluene	12.328	13163457	2447.037 ug/L
16) T 3-Nitrotoluene	13.588	5626717	822.697 ug/L

(f)=RT Delta > 1/2 Window

(m)=manual int.

Data Path : Z:\HPCHEM1\HPLC_N\Data\HN100515\
Data File : HN007557.D
Signal(s) : vwd1A.ch
Acq On : 05-Oct-2015, 15:26
Operator : UM/MA
Sample : G3697-01
Misc :
ALS Vial : 9 Sample Multiplier: 1

Instrument :
HPLC_N
ClientSampled :
38155-041515

Manual Integrations
APPROVED

MMDadoda
10/7/2015 4:00:17 PM

Integration File: autoint1.e
Quant Time: Oct 05 16:51:29 2015
Quant Method : Z:\HPCHEM1\HPLC_N\Methods\HN100515.M
Quant Title :
QLast Update : Mon Oct 05 14:10:20 2015
Response via : Initial Calibration
Integrator: ChemStation

Volume Inj. : 50 ul
Signal Phase : ZORBAX Extend-C18
Signal Info : 4.6 X 100mm 3.5-Micron 80A

