

Signal #1 : X:\HPCHEM1\HPLC N\DATA\HN101514\HN006349.D\VWD1A.CH Vial: 46
 Signal #2 : X:\HPCHEM1\HPLC N\DATA\HN101514\HN006349.D\VWD1A.CH
 Acq On : 16-Oct-2014, 10:20 Operator: HNP
 Sample : F4204-13 Inst : G1314A
 Misc : Multiplr: 1.00
 IntFile Signal #1: autoint1.e IntFile Signal #2: autoint2.e
 Quant Time: Oct 16 13:25 2014 Quant Results File: HN100214.RES

Instrument :
 HPLC_N
 ClientSampleId :
 YS19-SB46-0H-02-1014

Manual Integrations
 APPROVED

mohammad
 10/21/2014 10:21:23 AM

Quant Method : Z:\HPCHEM1\HPLC_N\METHODS\HN100214.M
 Title :
 Last Update : Fri Oct 03 10:34:01 2014
 Response via : Initial Calibration
 DataAcq Meth : 8330AGIP.M

Volume Inj. : 50 ul
 Signal #1 Phase : ZORBAX Extend-C18 Signal #2 Phase:
 Signal #1 Info : 4.6 X 100mm 3.5-M Signal #2 Info :

Compound	R.T.	Response	Conc Units

System Monitoring Compounds			
1) S 4-Nitroaniline	1.30	619008	155.744 ug/L m
Target Compounds			
9) T 2,4,6-Trinitrotoluene	6.59	955534	88.994 ug/L m

 Analyst Signature: _____ Analyst Name: _____ Date: _____

-----REASONS FOR MANUAL INTEGRATIONS-----

Poor resolution of peaks exhibited on chromatogram.Compound #:

Peak Integrated by software incorrectly.Compound #:

OTHER: _____ Compound #: _____

(f)=RT Delta > 1/2 Window (m)=manual int.

HN006349.D HN100214.M Thu Oct 30 05:18:34 2014

Quantitation Report

Signal #1 : X:\HPCHEM1\HPLC N\DATA\HN101514\HN006349.D\VWD1A.CH Vial: 46
 Signal #2 : X:\HPCHEM1\HPLC N\DATA\HN101514\HN006349.D\VWD1A.CH
 Acq On : 16-Oct-2014, 10:20 Operator: HNP
 Sample : F4204-13 Inst : G1314A
 Misc : Multiplr: 1.00
 IntFile Signal #1: autoint1.e IntFile Signal #2: autoint2.e
 Quant Time: Oct 16 13:25 2014 Quant Results File: HN100214.RES

Instrument :
 HPLC_N
 ClientSampleId :
 YS19-SB46-0H-02-1014

Manual Integrations
 APPROVED

mohammad
 10/21/2014 10:21:23 AM

Quant Method : Z:\HPCHEM1\HPLC_N\METHODS\HN100214.M
 Title :
 Last Update : Fri Oct 03 10:34:01 2014
 Response via : Multiple Level Calibration
 DataAcq Meth : 8330AGIP.M

Volume Inj. : 50 ul
 Signal #1 Phase : ZORBAX Extend-C18 Signal #2 Phase:
 Signal #1 Info : 4.6 X 100mm 3.5-M Signal #2 Info :

