

Signal #1 : X:\HPCHEM1\HPLC N\DATA\HN101714\HN006451.D\VWD1A.CH Vial: 36
 Signal #2 : X:\HPCHEM1\HPLC N\DATA\HN101714\HN006451.D\VWD1A.CH
 Acq On : 18-Oct-2014, 12:08 Operator: HNP
 Sample : F4312-16 Inst : G1314A
 Misc : Multiplr: 1.00
 IntFile Signal #1: autoint1.e IntFile Signal #2: autoint2.e
 Quant Time: Oct 21 18:17 2014 Quant Results File: HN100214.RES

Instrument :
 HPLC_N
 ClientSampleId :
 YS19-SS02P-1014

Manual Integrations
 APPROVED

mohammad
 10/30/2014 10:26:39 AM

Quant Method : Z:\HPCHEM1\HPLC_N\METHODS\HN100214.M
 Title :
 Last Update : Fri Oct 17 14:52:14 2014
 Response via : Initial Calibration
 DataAcq Meth : 8330AGIP.M

Volume Inj. : 50 ul
 Signal #1 Phase : ZORBAX Extend-C18 Signal #2 Phase:
 Signal #1 Info : 4.6 X 100mm 3.5-M Signal #2 Info :

Compound	R.T.	Response	Conc Units

System Monitoring Compounds			
1) S 4-Nitroaniline	1.31	685401	172.449 ug/L m
Target Compounds			
3) T RDX	1.68	465833	84.966 ug/L m

 Analyst Signature: _____ Analyst Name: _____ Date: _____

-----REASONS FOR MANUAL INTEGRATIONS-----

Poor resolution of peaks exhibited on chromatogram.Compound #:

Peak Integrated by software incorrectly.Compound #:

OTHER:

Compound #:

(f)=RT Delta > 1/2 Window

(m)=manual int.

HN006451.D HN100214.M

Thu Oct 30 09:47:26 2014

Quantitation Report

Signal #1 : X:\HPCHEM1\HPLC N\DATA\HN101714\HN006451.D\VWD1A.CH Vial: 36
 Signal #2 : X:\HPCHEM1\HPLC N\DATA\HN101714\HN006451.D\VWD1A.CH
 Acq On : 18-Oct-2014, 12:08 Operator: HNP
 Sample : F4312-16 Inst : G1314A
 Misc : Multiplr: 1.00
 IntFile Signal #1: autoint1.e IntFile Signal #2: autoint2.e
 Quant Time: Oct 21 18:17 2014 Quant Results File: HN100214.RES

Instrument :
 HPLC_N
 ClientSampleId :
 YS19-SS02P-1014

Manual Integrations
 APPROVED

mohammad
 10/30/2014 10:26:39 AM

Quant Method : Z:\HPCHEM1\HPLC_N\METHODS\HN100214.M
 Title :
 Last Update : Fri Oct 17 14:52:14 2014
 Response via : Multiple Level Calibration
 DataAcq Meth : 8330AGIP.M

Volume Inj. : 50 ul
 Signal #1 Phase : ZORBAX Extend-C18 Signal #2 Phase:
 Signal #1 Info : 4.6 X 100mm 3.5-M Signal #2 Info :

