

Signal #1 : Z:\HPCHEM1\HPLC_N\DATA\HN102314\HN006517.D\VWD1A.CH Vial: 39
 Signal #2 : Z:\HPCHEM1\HPLC_N\DATA\HN102314\HN006517.D\VWD1A.CH
 Acq On : 24-Oct-2014, 00:17 Operator: HNP
 Sample : F4325-14 Inst : G1314A
 Misc : Multiplr: 1.00
 IntFile Signal #1: autoint1.e IntFile Signal #2: autoint2.e
 Quant Time: Nov 5 7:34 2014 Quant Results File: HN100214.RES

Instrument :
 HPLC_N
 ClientSampleId :
 YS19-SB11-1014

Manual Integrations
 APPROVED

ugo
 11/3/2014 11:47:17 AM

Quant Method : Z:\HPCHEM1\HPLC_N\METHODS\HN100214.M
 Title :
 Last Update : Sat Oct 25 01:28:50 2014
 Response via : Initial Calibration
 DataAcq Meth : 8330AGIP.M

Volume Inj. : 50 ul
 Signal #1 Phase : ZORBAX Extend-C18 Signal #2 Phase:
 Signal #1 Info : 4.6 X 100mm 3.5-M Signal #2 Info :

Compound	R.T.	Response	Conc Units

System Monitoring Compounds			
1) S 4-Nitroaniline	1.30	611381	153.825 ug/L m
Target Compounds			
3) T RDX	1.69	130808	23.859 ug/L m

 Analyst Signature: _____ Analyst Name: _____ Date: _____

-----REASONS FOR MANUAL INTEGRATIONS-----

___Poor resolution of peaks exhibited on chromatogram.Compound #: _____

___Peak Integrated by software incorrectly.Compound #: _____

___OTHER: _____ Compound #: _____

(f)=RT Delta > 1/2 Window (m)=manual int.

HN006517.D HN100214.M Sat Nov 08 00:21:28 2014

Quantitation Report

Signal #1 : Z:\HPCHEM1\HPLC_N\DATA\HN102314\HN006517.D\VWD1A.CH Vial: 39
 Signal #2 : Z:\HPCHEM1\HPLC_N\DATA\HN102314\HN006517.D\VWD1A.CH
 Acq On : 24-Oct-2014, 00:17 Operator: HNP
 Sample : F4325-14 Inst : G1314A
 Misc : Multiplr: 1.00
 IntFile Signal #1: autoint1.e IntFile Signal #2: autoint2.e
 Quant Time: Nov 5 7:34 2014 Quant Results File: HN100214.RES

Instrument :
 HPLC_N
 ClientSampleId :
 YS19-SB11-1014

Manual Integrations
 APPROVED

ugo
 11/3/2014 11:47:17 AM

Quant Method : Z:\HPCHEM1\HPLC_N\METHODS\HN100214.M
 Title :
 Last Update : Sat Oct 25 01:28:50 2014
 Response via : Multiple Level Calibration
 DataAcq Meth : 8330AGIP.M

Volume Inj. : 50 ul
 Signal #1 Phase : ZORBAX Extend-C18 Signal #2 Phase:
 Signal #1 Info : 4.6 X 100mm 3.5-M Signal #2 Info :

